

Arbor holders including pilot drill for HSS and HSS Co 8 bi-metal hole saws

Packing unit: in individual carton

Hole saws Ø mm	Type	Shank Ø mm	Shank shape	Thread	Article no.	Price / each €
14,0 - 30,0	A 1	11,0	⬡	1/2" x 20	106 201	
32,0 - 210,0	A 2	11,0	⬡	5/8" x 18	106 202	
14,0 - 30,0	A 4	6,0	○	1/2" x 20	106 204	
14,0 - 30,0	A 5	9,5	⬡	1/2" x 20	106 210	
32,0 - 210,0	A 6	9,5	⬡	5/8" x 18	106 209	
32,0 - 210,0	A 7	10,0	SDS-Plus	5/8" x 18	106 211	



No. 106 202

Adapter for arbor holders, type A1 / A4 / A5

Packing unit: individual plastic pack

Description	Article no.	Price / each €
Adapter to support HSS and HSS Co 8 bi-metal hole saws from Ø 32 to Ø 210 mm	106 212	




No. 106 212


Accessories for HSS and HSS Co 8 bi-metal hole saws

Packing unit: individual plastic pack

Description	Article no.	Price / each €
Pilot drill HSS, ground, Ø 6.35 mm x 102 mm and split point in accordance with DIN 1412 C (A4)	106 207	
Pilot drill HSS, ground, Ø 6.35 mm x 82 mm and split point in accordance with DIN 1412 C (A1 + A2 + A5 + A6 + A7)	106 206	
Extension 300 mm, arbors for A1 + A2 shank shape ⬡ 11 mm	106 205	
Ejector spring	106 208	



No. 106 207



No. 106 205



No. 106 208

Sets of HSS bi-metal hole saws in plastic cases

Type	Description	Article no.	Price / set €
PK 1	For plumbers 6 HSS bi-metal hole saws Ø 19 - 22 - 29 - 38 - 44 - 57 mm + 2 arbor holders A2 and A4	106 301	
PK 2	For plumbers 9 HSS bi-metal hole saws Ø 19 - 22 - 29 - 35 - 38 - 44 - 51 - 57 - 64 mm + 2 arbor holders A2 and A4	106 306	



Nr. 106 306