

## PCB Mount Miniature Speakers



- PCB mounting
- 1200 Hz frequency

Designed to satisfy the need for a small, PCB mountable speaker transducer for use in keyboards. It has a low profile and a sound output suitable for an office-type environment.

Mfrs. List No.	AST-030COMR-R
Rated Input Power	0.15W
Maximum Input Power	0.3W
Impedance	100 $\Omega$ $\pm$ 20%
Sound Pressure Level	80dB
Resonant Frequency	1200Hz $\pm$ 10%
Frequency Range	1200Hz to 10000Hz
Operating Temperature	-20°C to +60°C
Dimensions	$\varnothing$ 29.7mm x 12.7mm
Weight	8.5g
Pin Pitch x Pin Dia.	15.0 x $\varnothing$ 1.0mm

338904.473091

Mfrs. List No.	Order Code	Price Each
AST-030COMR-R	119-2971 ●	