


PC card drilling dimensions(after plating)  
(thickness 1.60±0.20mm)

SHELL	A± 0.38	B± 0.12	C± 0.10	D± 0.25	E± 0.07
09	30.81	24.99	16.96	16.21	10.96
15	39.14	33.32	25.18	24.54	19.18
25	53.03	47.04	39.12	38.25	33.12

GENERAL CHARACTERISTICS : SEE DRAWING C01-8646-0000

Core range		
SHELL	PART NUMBER	DESIGNATIONS
09	D09S24A4GV00	RECEPTACLE 9 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK UNC 4.40-ELEC.CONTIN.-PERFORM. LEVEL PL3
15	D15S24A4GV00	RECEPTACLE 15 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK UNC 4.40-ELEC.CONTIN.-PERFORM. LEVEL PL3
25	D25S24A4GV00	RECEPTACLE 25 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK UNC 4.40-ELEC.CONTIN.-PERFORM. LEVEL PL3



d	16/04/03	removal of sheet 2/2	--
ISS	DATE	Latest modification by : BART.5	MOD N°
Designed by: JOUBERT date 21/12/00			Type of drawing: CUSTOMER
TITLE : RECEPTACLE STD EUROPE			SHEET 1/1
SCALE: 2			straight solder type for PCB 1.60mm
	<b>FRAMATOME CONNECTORS FRANCE</b> Rue Louis Breguet - BP 05 72024 LE MANS Cedex Tel. 33 (16) 43.84.08.43		This document is the property of FRAMATOME CONNECTORS FRANCE It must not be reproduced or communicated without permission in writing from the owners
	FORMAT <b>A3</b>	DRG N° <b>C01-8646-0752-1</b>	PROJECT <b>M94D002</b>