

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [63811-7100](#)
Status: **Active**
Description: HAND CRIMP TOOL

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	T0102
Comments	Field Repair, See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Product Name	PremiumGrade™
Survey	www.molex.com//review/apptool_survey.html
Tool Type	Handtool

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-6381171HM, TM-638000029, TM-638000029CN, TM-638000029DE, TM-638000029FR, TM-638000029IT, TM-638000029JP, TM-638000029KR, TM-638000029MY, TM-638000029PL, TM-638000029RU, TM-638000029SK, TM-638000029SP, TM-638000029TH, TM-638000029TW, TM-638000029VN



EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

T0102Series

Use With

Loose piece terminals

Application Tooling | **FAQ**

Description	Product #
2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1433, Female, with Tin (Sn) over Copper Plated Brass Contact, 24-28 AWG, Reel, with Dimple	0039000315
2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1433, Female, with Tin (Sn) over Copper Plated Brass	0039000316

Contact, 24-28 AWG,
Bag, with Dimple
2.36mm Diameter, 0039000317
Standard .093" Pin
and Socket Crimp
Terminal, Series
1433, Female,
with Tin (Sn) over
Copper Plated Brass
Contact, 24-28 AWG,
Reel
2.36mm Diameter, 0039000318
Standard .093" Pin
and Socket Crimp
Terminal, Series
1433, Female,
with Tin (Sn) over
Copper Plated Brass
Contact, 24-28 AWG,
Bag
2.36mm Diameter, 0039000323
Standard .093"
Pin and Socket
Crimp Terminal,
Series 1434, Male,
with Tin (Sn) over
Copper Plated Brass
Contact, 24-28 AWG,
Reel
2.36mm Diameter, 0039000324
Standard .093"
Pin and Socket
Crimp Terminal,
Series 1434, Male,
with Tin (Sn) over
Copper Plated Brass
Contact, 24-28 AWG,
Bag
Claspcn™ Crimp 0002081103
Terminal Socket, Tin
(Sn) Plated Brass
Contact, 24-30 AWG,
Reel
Claspcn™ Crimp 0002081104
Terminal Socket, Tin
(Sn) Plated Brass
Contact, 24-30 AWG,
Bag
2.36mm Diameter, 0002091615
Standard .093"
Pin and Socket
Crimp Terminal,
Series 42477,
Female, with Tin
(Sn) Plated Contact,
High Current/Low
Engagement Force,
14-18 AWG, Reel
2.36mm Diameter, 0002092611
Standard .093" Pin
and Socket Crimp
Terminal, Series
42478, Male, with Tin
(Sn) Plated Contact,
High Current/Low

Engagement Force,
14-18 AWG, Reel
2.36mm Diameter, 0039000322
Standard .093" Pin
and Socket Crimp
Terminal, Series
1433, Female, with
Gold (Au) over
Nickel Plated Brass
Contact, 24-28 AWG,
Bag
2.36mm Diameter, 0039000325
Standard .093" Pin
and Socket Crimp
Terminal, Series
1434, Male, with
Gold (Au) over
Nickel Plated Brass
Contact, 24-28 AWG,
Reel
2.36mm Diameter, 0039000326
Standard .093" Pin
and Socket Crimp
Terminal, Series
1434, Male, with
Gold (Au) over
Nickel Plated Brass
Contact, 24-28 AWG,
Bag

This document was generated on 04/17/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION