

Technical Characteristics

Certifications	UL Listed (E164862 / NLDX) - CSA Certified (LR43364 3211 04) - IEC Rated (60647-4) - CE Marked - RoHS Compliant
Contacteur Type	Non-Reversing
Inductive Amperes (AC3)	9A
Resistive Amperes (AC1)	20A
Horsepower Rating (1-Phase)	0.5HP@115Vac - 1HP@230Vac
Horsepower Rating (3-Phase)	2HP@200/230Vac - 5HP@460Vac - 7.5HP@575Vac
Marketing Trade Name	TeSys
Maximum Voltage Rating	600 Vac
Mounting Style	35mm DIN Rail
Number of Poles	3-Pole (3 NO)
Coil Voltage Code	U7
Coil Consumption Sealed	7.5 VA
Coil Voltage	240Vac@50/60Hz
Coil Consumption Inrush	70 VA
Weight	0.71 lbs (0.32 kg)
Power Wire Size	#10 to #18 AWG
Control Terminal Torque	15 lb-in (1.7 Nm)
Power Terminal Torque	15 lb-in (1.7 Nm)
Terminal Type	Screw Clamp
Control Wire Size	#10 to #18 AWG
Type	TeSys D

Shipping and Ordering

Category	22345 -
Discount Schedule	I12
GTIN	00785901207009
Package Quantity	1
Weight	0.78 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	FR

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.