



Laser Diode Modules: By Wavelength

Red Lasers

Model	Class	Lens	Beam Shape	Wavelength (nm)	Power (mW)	Beam Diameter (mm)	Focus	Operating Voltage (DC)
150-3-635	IIIa	Glass	Spot	635	3	<1	Adj.	4.5-9
150-1-635	II	Glass	Spot	635	<1	<1	Adj.	4.5-9
2309-3-650	IIIa	Plastic	line	650	3	1	Fixed	3 or 4.5