


Please wait for menu to be constructed

Non-Insulated Terminals

Non-Insulated Ring



* Brazed Seam, Lolly-Pop Style Tongue

Dimensional Images

Dimension Information In F.P.S (U.S)

[Display in metric standards \(C.G.S\)](#)

Catalog No	Dim A (In.)	Dim B (In.)	Dim C (In.)	Dim M (In.)	Insulation Type	Plating	Stock Thickness (In.)	Tongue Shape	Bolt Hole
K973	2.080	0.930	0.540	1.690	Non Insulated	Tin Plated	0.060	Ring Connector	3/8

AN-Aircraft Wire

Note: Not available on Mylar Tape.

Most standard bulk catalog numbers can be put on Mylar Tape for reel fed applications (i.e. 12050 tool and application dies).

Please put the suffix M for Mylar Tape RA2573M. (Bulk number 1000 and 500 packages.)

Tools

Used

Packaging Information

Catalog#	Unit Quantity	Standard Quantity Package	Weight (lbs.)	Weight UOM
K973	50	250	7.660	Per 100

Listed / Certified By



UL Listed

(Catalog# K973)
(File# 9809)



CSA Certified

(Catalog# K973)
(File# 4503,7222)

[Smart Search Results](#) [View Product Category](#)

[Print Back](#)