

PVC Strain Relief

**Description**

- Component:
Press-Fit Version
- bend protection

Weblinks

[pdf](#), [html](#), [General Product Information](#), [Approvals](#), [RoHS](#), [CHINA-RoHS](#), [Mating Connectors](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Accessories](#)

Variants

Suitable for	Color	Für Leitung mit Mantelaus- sendurchmesser	Tüllenlänge [mm]	Order Number
1611, 1612, 1651, 1652, 4013, 4020, 4021, 4022, 8101, 8111, 9009, 9013	black / grey / white	8.7 mm	39.4	4311.0053
0101, 0102, 0104, 0104U, 0106, 0112	black / grey / white	10.0 mm	39	4311.0063
0101, 0102, 0104, 0104U, 0106, 0112	black / grey / white	8 mm	38	4311.0064
4012	black / grey / white	8 mm	37.5	4311.0067
1611, 1612, 1651, 1652, 4013, 4020, 4021, 4022, 8101, 8111, 9009, 9013	black / grey / white	10.0 mm	39	4311.0068
0101, 0102, 0104, 0104U, 0106, 0112	black or grey	8 - 10 mm	40.3	4311.9301
1611, 1612, 1651, 1652, 4013, 4020, 4021, 4022, 8101, 8111, 9009, 9013	black / grey / white	8,7 - 10 mm	40.3	4311.9305
4012	black / grey / white	8 - 10 mm	36.7	4311.9307
4012	black / grey / white	10.0 mm	37	4311.9322
1251, 3017	black / grey / white	6,5 mm	30	4311.9324

Packaging unit 100 Pcs