

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [50-84-2150](#)
Status: **Active**
Overview: [MLX™ Power Connectors](#)
Description: 2.13mm Diameter MLX™ Pin and Socket Receptacle, 15 Circuits

Documents:

[3D Model](#) [Product Specification PS-42022-0001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Crimp Housings
 Series [42022](#)
 Application Power, Wire-to-Wire
 Comments Glow Wire Equivalent Part Number [366440008](#). Current – Maximum per contact 20A if used with [36663](#) and [36664](#) terminal
 Overview [MLX™ Power Connectors](#)
 Product Name MLX™

Physical

Circuits (maximum) 15
 Circuits Detail 15
 Color - Resin Natural
 Flammability 94V-2
 Gender Female
 Glow-Wire Compliant No
 Keying to Mating Part None
 Lock to Mating Part Yes
 Material - Resin Nylon
 Number of Rows 3
 Packaging Type Carton
 Panel Mount Yes
 Pitch - Mating Interface 6.35mm
 Polarized to Mating Part Yes
 Stackable No
 Temperature Range - Operating -55°C to +105°C

Electrical


Current - Maximum per Contact 20A

Material Info

Old Part Number [42022-15A](#)
 UPC 800753755307

Reference - Drawing Numbers

Product Specification PS-42022-0001
 Sales Drawing SD-36644-001, SD-42022-**



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[42022Series](#)

Mates With

[42021](#) MLX™ Power Crimp Housing Plug

Use With

MLX Crimp Terminal [42023](#) , [42024](#)