## PRODUCT SPECIFICATION

Brand KASP

Product Range Heavy Duty Combination Padlock

Catalogue number 117

**Date** 19/03/2009



#### **Range Description**

Resettable combination padlocks

#### **Features**

- Hardened Steel Shackle Extra protection against hacksaw & cropping attacks
- Double Bolted Locking Mechanism Extra strength to resist torsion & pull attacks
- Anti Manipulation Locking System Protects against manipulation attack
- 4 Dial Resettable Combination Resettable combination for added convenience & security
- Rust Free Internal Components Extra resistance against corrosion

The padlock is supplied display packed, in sealed blister packs.





Item Number	Item Description	EAN No	Commodity	Carton
			code	Qty
K11750D	Heavy Duty Combination Padlock 50mm – display packed	5013969901771	83011000	6

Technical product information	Body – Die Cast, Chrome plated
Illioillation	Shackle - Hardened steel, Chrome plated
	Lacting machanism. Double helted A diel combination lection
	<b>Locking mechanism -</b> Double bolted, 4 dial combination locking mechanism featuring an anti-manipulation locking system to prevent
	intelligent manipulation attack.

#### To open the padlock:

1) Using the correct combination code, open the padlock by aligning the dial wheels with the indicators on the lock body (pre-set factory combination code 0-0-0-0) and depress the shackle

#### To lock the padlock:

1) Whilst in the open position, scramble the dial wheels and depress the shackle into the body of the padlock until it locks

#### To reset the lock to a combination of your choice:

- 1) Open the padlock using the preset combination code
- 2) Insert the change key into the keyhole on the side of the padlock
- 3) Firmly press the key into the keyhole and turn 90 degress clockwise or anti-clockwise. [IMPORTANT: Ensure the change key is fully depressed to avoid losing the combination]
- 4) With the change key held at 90 degrees, reset the dials wheels to a combination of your choice (we recommend that you record your new combination code and store it in a safe place)
- 5) With your new combination code set, turn the change key through 90 degrees back to its original position and withdraw it from the key hole
- 6) Lock the padlock by scrambling the dial wheels and depressing the shackle into the body of the padlock until it locks

### Security rating:

	Security
Type	rating
K11750D	6

#### Shackle Dimensions:

	Shac	Shackle			
Dimensions mm	Dia	Internal width	Internal height	Width	
K11750D	8	25	25	50	

**Use environment -** Normal outdoor use  $\sqrt{\sqrt{}}$ 

**Recommended applications-** Lockers, sheds, gates, garages

Standards compliance	None applicable
User health and safety information	None applicable
RoHS/WEEE	This product range does not fall within the scope of RoHS or WEEE
compliance	regulations
Material safety data	None applicable
Warranty	KASP padlocks are guaranteed against defects in manufacture and/or materials for 10 years
	Damage caused through inappropriate use or attempted break in is not covered
Country of origin	Taiwan

## **Dimensional details**

	Product only				Product on primary packaging			
Item	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
K11750D	50	25	75	246	118	27	186	290

	Shelf box (s	secondary pa	Euro Pallet Wi x Hi	data		
Item			Gross weight g	No of cartons on base	Number of rows high	
K11750D	130	200	115	1855		

# Packaging waste details

	Primary Pa	ckaging	Secondary packaging					
Item	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
K11750D	36	Blister	8	Backing card			104	Box