

Model	4E-115
Size	119mm×119mm×38mm
	(4.69"×4.69"×1.50)
Rated Voltage	115 V
Frequency	50 / 60 Hz
Input Power	24 / 22 W
Max.Rated Current	250 / 240 mA
Speed	2650 / 3000 RPM
Maximum Air Flow	2.33 / 2.71 m ³ /min.
Maximum Air Flow	82.4 / 95.6 CFM
Maximum Pressure	6.7 / 7.4 mmH ₂ O
Maximum Pressure	0.26 / 0.29 InchH ₂ O
Noise	41 / 45 dB
Weights	600 g
Model	4E-230
Size	119mm×119mm×38mm
	(4.69"×4.69"×1.50)
Rated Voltage	230V
Frequency	50 / 60 Hz
Input Power	22 / 21 W
Max.Rated Current	140 / 130 mA
Speed	2650 / 3000 RPM
Maximum Air Flow	2.33 / 2.71 m ³ /min.
Maximum Air Flow	82.4 / 95.6 CFM
Maximum Pressure	6.7 / 7.4 mmH ₂ O
Maximum Pressure	0.26 / 0.29 InchH ₂ O
Noise	41 / 45 dB
Weights	600 g