



<b>wireXpress Part No.</b>	6TXL-2001-0
<b>Manufacturer</b>	ALL GENERIC VENDORS
<b>Manufacturer Part Nos.</b>	- -
<b>Description</b>	20 TXL 7 STR BC XLP BLK SAE J1128 ROHS SAE J1128-TYPE TXL 18 AWG BLK. FORD ESB-M1L123, CHRYSLER MS-8288, PACKARD M-3075. USE FOR ENGINE & BODY WIRING HARNESSSES IN PASSENGER CARS, TRUCKS & OFF-THE-ROAD VEHICLES WHERE LIGHT WEIGHT, SMALL BUNDLE SIZE & HEAT RESISTANCE ARE REQUIRED.
<b>Attributes</b>	
<b>Type:</b>	TXL-THIN WALL CROSSLINKED POLYETHYLENE
<b>SAE Spec:</b>	J1128
<b>Gauge: AWG</b>	20 AWG (AMERICAN WIRE GAUGE)
<b>CONDUCTOR: Number</b>	1 CONDUCTOR
<b>Stranding</b>	7 STRANDS IN EACH CONDUCTOR
<b>Material</b>	BARE COPPER
<b>INSULATION: Material</b>	XLPE-CROSS LINKED POLYETHYLENE
<b>Color</b>	BLACK
<b>Shielded:</b>	NOT SHIELDED
<b>Temperature Rating:</b>	125 DEGREES CENTIGRADE (257 F)
<b>RoHS Compliant:</b>	YES
<b>Unspsc Code</b>	26121508