

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022414032

Status:

Active

Overview:

kk

Description:

2.54mm (.100") KK® IDT Double Cantilever Contact, 3 Circuits, Tin (Sn), Feed-To, 24 Stranded, Solid, Fused, Topcoat, and 26 Fused and Topcoat, Green ID Stripe

Documents:

3D Model

Drawing (PDF)

Product Specification PS-7720-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Comments

Crimp Quality Equipment

Overview

Product Name

IDT and Solder Connectors

7720

Double Cantilever contact

Yes

kk

KK®

Physical

Circuits (Loaded)

Color - Resin

Durability (mating cycles max)

Flammability

Gender

Glow-Wire Compliant

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Polarized to Mating Part

Temperature Range - Operating

Termination Interface: Style

Wire Size AWG

3

Natural

5

94V-2

Female

No

Yes

Phosphor Bronze

Tin

Tin

Nylon

1

Bag

No

2.54mm (.100")

Yes

0°C to +75°C

IDT or Pierce

24 Solid, 24 Stranded, 24 Stranded Topcoat, 26 Stranded Topcoat

Electrical

Current - Maximum per Contact

Voltage - Maximum

4A

250V

Material Info

Old Part Number

A-7720-E03H154B

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-7720-001

SD-7720-001



image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

7720Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Insertion Tool for 2.54mm (.100") Pitch KK® IDT Crimp Terminals	0638133504
Changehead for 7720 and 7720s Connector Range, Color Bar In, Feed-To Only	0690080225
Arbor Press Fixture for 7720 and 7720s Insulation Displacement Housings, 2-28	0690200320

Circuit, 24-28 AWG
Wire/ Ribbon Cable
IDT - Manual Press 0011200179
IDT - Semi-automatic0011200771
- Bench-Top
Terminator
IDT - Semi-automatic0623000100
- Bench-Top
Terminator

This document was generated on 09/23/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION