

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [08-50-0185](#)
Status: **Active**
Description: KK® Trifurcon™ Crimp Terminal 7258, 22-26 AWG, Bag, Brass Tin (Sn)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-40-02 \(PDF\)](#)

General

| | |
|-------------------------|----------------------|
| Product Family | Crimp Terminals |
| Series | 7258 |
| Application | Power |
| Crimp Quality Equipment | Yes |
| Product Name | KK®, Trifurcon™ |

Physical

| | |
|--------------------------------|----------------------|
| Gender | Female |
| Material - Metal | Brass |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Packaging Type | Bag |
| Plating min - Mating | 2.540µm |
| Plating min - Termination | 2.540µm |
| Termination Interface: Style | Crimp or Compression |
| Wire Insulation Diameter | 1.65mm max. |
| Wire Size AWG | 22, 24, 26 |
| Wire Size mm² | N/A |

Material Info

| | |
|-----------------|--------------|
| Old Part Number | 7258-(P909)L |
|-----------------|--------------|

Reference - Drawing Numbers

| | |
|-----------------------|----------|
| Product Specification | PS-40-02 |
| Sales Drawing | SD-7258 |



EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Reviewed**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[7258Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

| Description | Product # |
|-------------------------------------|----------------------------|
| Hand Crimp Tool for Crimp Terminals | 0638117400 |