

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130244-1201](#)
Status: **Active**
Overview: SolarSpec™ Junction Box and Cable Assemblies
Description: SolarSpec™ DC Socket Female Housing Kit, 5 pieces, includes Socket Contact, 4.00 to 6.00mm2 (10-12 AWG) Cable, Cable Opening 8.40mm

Documents:

Drawing (PDF)	Application Specification AS-130244-001 (PDF)
Application Specification (PDF)	Packaging Specification PK-130244-021 (PDF)
Product Specification PS-130244-001 (PDF)	RoHS Certificate of Compliance (PDF)



image - Reference only

General

Product Family	Crimp Housings
Series	130244
Application	Power, Wire-to-Wire
Overview	SolarSpec™ Junction Box and Cable Assemblies
Product Name	SolarSpec™

Physical

Circuits (maximum)	1
Color - Resin	Black
Gender	Socket
Glow-Wire Compliant	No
Material - Resin	Polycarbonate
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	N/A
Ports	1
Temperature Range - Operating	-40°C to +80°C

Electrical

Current - Maximum per Contact	30A
-------------------------------	-----

Material Info

UPC	884982367548
-----	--------------

Reference - Drawing Numbers

Application Specification	AS-130244-001
Packaging Specification	PK-130244-021
Product Specification	PS-130244-001
Sales Drawing	SD-130244-021

EU RoHS

ELV and RoHS Compliant
REACH SVHC
 Not Reviewed
Low-Halogen Status
 Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[130244Series](#)

Mates With

[13022441202](#) , [1302441204](#)