

För icke direkt toleranssatta mått gäller toleransklass
 General tolerances if not otherwise stated


Rev	Change order	Change: A = Added W = Was D = Deleted	Date	Sign
1	1022154000	A 3x 4101-3490	050214	TGW

NOM DIM MM		TOL CLASS		
From	To	A	B	C
(1)	6	±0.05	±0.1	±0.2
(6)	30	±0.1	±0.2	±0.5
(30)	100	±0.15	±0.3	±0.8
(100)	300	±0.2	±0.5	±1.2
(300)	1000	±0.3	±0.8	±2

Hål / Holes H13

Skarpa kanter brutna där ej annat anges.
 No sharp edges unless otherwise specified.

Övriga generella toleranser enligt ritning 4100-4644.
 Additional general tolerances in accordance with drawing 4100-4644.



Denna ritning är Pressmaster AB:s egendom. Skyddad av gällande lag.
 This drawing is the property of Pressmaster AB. Protected in accordance with prevailing law.

Packas enligt förpackningsritning 4101-3770
 Packed according to drawing 4101-3770

4101-3495
 A
 B

4300-3164/AAA	4101-3769A POSITION A	4101-3583	4101-3585	4101-3036	4101-3490
ART.NR.VAR.	A	B	C	D	E

Material		Behandling/Treatment			Status	
Konstr/Design		Ritad/Drawn	Datum/Date	Skala/Scale	Kontr/Checked	Godk/Approved
TGW		TGW	2005-02-14	1:1	SE	NE
pressmaster®				Benämning/Denomination		Vikt/Weight,gram
50301 REG NR FM3607				Verktygssats mobile tool		Art grp 012
				Ferrule kit		REV 001
				Ritn nr/Drawing no		43003164