


BitBuddy 49, mixed, 7-pcs.


- Housing:** Box of impact resistant, glass-fibre reinforced polyamide - permanently robust.
Bit clamping element with push buttons.
- Bits:** 49er MaxxTor bits.
- Geometry:** Length torsion zone individually matched to the profile.
Precision-milled profile for perfect fit and maximum performance.
- Application:** Compact bit box with the most common bits. Ideal for frequently varying fastening applications within one work sector.
Push the Wiha logo slightly, and the bits are ready to be inserted into the bit holder!
Plug & Work & Store - Maximum efficiency due to direct bit insertion without any problems. Insert, work, store.
- Extra:** Always ready to use - easily fits into trouser pockets or the belt clip.

Ord.No.	
36926	5

Ord.No.	Quantity	⊕	⇄	⊕	⊗
36829	1	PH2	49		
36831	1		49	PZ1	
36832	1		49	PZ2	
36833	1		49	PZ3	
36839	1		49		T15
36840	1		49		T20
36841	1		49		T25