

## Twist drill sets DIN 338 type N HSS rolled / HSS-TiN in plastic bit-box

19-piece set of twist drills DIN 338 type N HSS rolled  
Ø 1,0 mm up to 10,0 mm in increments 0,5 mm

**Art. no. A 205 225**

**Packing unit = 25 pcs.**

19-piece set of twist drills DIN 338 HSS-TiN ground  
Ø 1,0 mm up to 10,0 mm in increments 0,5 mm

**Art. no. A 250 225 T**

**Packing unit = 25 pcs.**



## Drill set with twist drills DIN 338 type N HSS rolled, masonry drills and wood drills in plastic combi bit-box

18-piece set of drills  
6 twist drills DIN 338 type N HSS rolled  
Ø 3,0 - 4,0 - 5,0 - 6,0 - 8,0 - 10,0 mm

6 masonry drills DIN 8039  
Ø 3,0 - 4,0 - 5,0 - 6,0 - 8,0 - 10,0 mm

6 wood drills  
Ø 3,0 - 4,0 - 5,0 - 6,0 - 8,0 - 10,0 mm

**Art. no. A 205 226**

**Packing unit = 25 pcs.**



## Twist drill sets DIN 345 Typ N HSS in steel case

10-piece set of twist drills DIN 345 Typ N HSS  
Ø 14,0 / 15,0 / 16,0 / 17,0 / 18,0 /  
19,0 / 20,0 / 21,0 / 22,0 / 23,0 mm

**Art. no. A 204 001**

**Packing unit = 25 pcs.**

10-piece set of twist drills DIN 345 Typ N HSS  
Ø 14,0 / 16,0 / 18,0 / 20,0 / 22,0 /  
24,0 / 25,0 / 26,0 / 28,0 / 30,0 mm

**Art. no. A 204 002**

**Packing unit = 25 pcs.**

