

Twist drill magazine DIN 338 type N HSS rolled in steel case

170-piece set of twist drills DIN 338 type N
HSS rolled

10 pcs. Ø 1,0 - 8,0 mm in increments of 0,5 mm
5 pcs. Ø 8,5 - 10,0 mm in increments of 0,5 mm

Art. no. A 205 200

Packing unit = 5 pcs.



Twist drill magazine DIN 338 type N HSS ground in steel case

170-piece set of twist drills DIN 338 type N
HSS ground

10 pcs. Ø 1,0 - 8,0 mm in increments of 0,5 mm
5 pcs. Ø 8,5 - 10,0 mm in increments of 0,5 mm

Art. no. A 214 200

Packing unit = 5 pcs.



Twist drill magazine DIN 338 type N HSS Co 5 ground in steel case

170-piece set of twist drills DIN 338 type N
HSS Co 5 ground, with split point

10 pcs. Ø 1,0 - 8,0 mm in increments of 0,5 mm
5 pcs. Ø 8,5 - 10,0 mm in increments of 0,5 mm

Art. no. A 215 200

Packing unit = 5 pcs.

