3M

28 Acetate Cloth Tape

Data Sheet

Product Description

$3M^{TM}$ 28 Acetate Cloth Tape is an aesthetically pleasing tape which offers excellent conformability in coil wrapping applications up to 105° C. Acetate cloth tapes also offer excellent absorption of resins and varnishes.

Like all 3M insulating tapes, 28 tape is available in standard and custom widths and lengths. Standard length is 72 yards.

Applications

Conformable; for use as coil cover: Printable.

Properties Typical Values

Adhesive	Thermosetting Rubber
Operating Temperature	105°C/221°F
Color	White
Total Thickness	8.0 mil/0,203 mm
Dielectric Breakdown	2500 volts
Insulation Resistance	2 x 10 ⁴ megohms
Breaking Strength	40 lb./in (70 N/10 mm)
Elongation (% at break)	10
Electrolytic Corrosion Factor	1.0
Adhesion to Steel	40 oz/in (4.4 N/10 mm)

Technical information provided consists of typical product data and should not be used for specification purposes. Unless otherwise noted, all tests are performed at room temperature.

Important Notice

Technical information provided by 3M is based on experience and/or tests believed to be reliable, but their accuracy is not guaranteed and the results may not be relevant to every user's application. For this reason 3M does not accept responsibility or liability, direct or consequential, arising from reliance upon any information provided and the user should determine the suitability of the products for their intended use. Nothing in this statement will be deemed to exclude or restrict 3M's liability for death or personal injury arising from its negligence. All questions of liability relating to 3M products are governed by the seller's terms of sale subject where applicable to the prevailing law

If any goods supplied or processed by or on behalf of 3M prove on inspection to be defective in material or workmanship, 3M will (at its option) replace the same or refund to the Buyer the price paid for the goods or services. Except as set our above, all warranties and conditions, whether express or implied, statutory or otherwise are excluded to the fullest extent permissible at law.

 $3\mbox{M}$ and Scotchcast are trademarks of the $3\mbox{M}$ Company. Printed in the UK.

© 3M United Kingdom PLC, 1999

3M United Kingdom PLC Electrical Products Group Hudson Road Bedford MK41 0HR Tel: 01234 268868 Fax: 01234 229433

3M Ireland Electrical products Group 3M House, Adelphi Centre Dun Loaghaire, CO. Dublin, Ireland Tel: (01) 2803555

Fax: (01) 2803509



Jan. 2000