



Speed, Performance, Value - The Right Balance

- RS-232 interface
- Internal counting resolution 1:400,000
- Preset tare function
- Full range tare
- Zero Tracking
- Memory accumulation
- Adjustable filters
- Pre-set counting with alarm
- Date and time
- Large backlit LCD displays
- Simple user-friendly operation
- Precision load cell technology
- Splashproof to protect from accidental spills
- Full colour coded keypad with numeric entry
- Large stainless steel pan
- Easy to use keypad
- Non-slip adjustable feet
- Overload protection
- Easy access to the rechargeable battery
- External calibration
- Rechargeable battery up to 90 hours operation
- Auto sleep / power down function to save battery life
- Low battery indication
- AC Adapter
- Weighing
- Weight accumulation
- Parts counting
- Check counting
- Count accumulation



Technical Specifications

Model	CBC 4	CBC 8	CBC 16	CBC 32	CBC 48
Maximum capacity	4000g	8000g	16kg	32kg	48kg
Readability	0.1g	0.2g	0.5g	1g	2g
Tare range	-4kg	-8kg	-9.9995kg	-32kg	-48kg
Repeatability (S.D.)	0.1g	0.2g	0.5g	1g	2g
Linearity (±)	0.2g	0.4g	1g	2g	4g
Pan size	225x275mm				
Units of measurement	Gram (g)		Kilogram (kg)		

General Specifications

Internal counting resolution	1:600,000
Functions	Parts counting, weighing, memory accumulation, preset count with alarm
Typical stabilisation time	2 Sec
Calibration	Automatic External
Display	3 x 6 digits LCD digital displays
Power supply	Rechargeable battery or mains power
Operating temperature	0°C - 40°C
Housing	ABS plastic, stainless steel platform
Overall dimensions (wxdxh)	315x355x110mm
Net weight	4.1kg

Key Accessories

- In-use Cover
- In-Use Cover pack of 10
- Adam Printer
- Thermal Paper Roll for Adam Printer
- AdamDU - Data Collection Program
- RS-232 to PC Cable
- In-Use Cover pack of 5
- RS-232 to USB Interface Cable (must be ordered with 3074010266 RS232 cable)
- Hard Carry Case with Lock
- ATP Thermal Printer
- Thermal Paper for ATP



Adam Equipment - offices worldwide

www.adamequipment.com