



Ø2mm stainless test pin

Ø4mm plug

PA66 plastic material+PVC

Test range: 0°-40° CAT III 1000V/CAT IV 600V 10A

DESCRIPTION	Test Probe	TENMA®				VERSION	A	DATE	
MODEL NO.	72-9330					DRAWING			
PART NO.		TOLERANCE	±0.05	SCALE	1:1	CHECKED			
DRAWING NO.		3RD.ANGLE		UNIT	M/M	APPROVED			