


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [50079-8100](#)
Status: **Active**
Overview: [PicoBlade™](#)
Description: 1.25mm Pitch PicoBlade™ Crimp Terminal, 26-28 AWG, Bag

Documents:

3D Model	Product Specification PS-51021-023 (PDF)
Drawing (PDF)	Product Specification PS-51021-024 (PDF)
Product Specification PS-51021-001 (PDF)	Product Specification PS-51021-025 (PDF)
Product Specification PS-51021-002 (PDF)	Product Specification PS-51021-026 (PDF)
Product Specification PS-51021-009 (PDF)	Product Specification PS-51021-027 (PDF)
Product Specification PS-51021-010 (PDF)	Product Specification PS-51021-028 (PDF)
Product Specification PS-51021-011 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-51021-022 (PDF)	



General

Product Family	Crimp Terminals
Series	50079
Application	Signal
Crimp Quality Equipment	Yes
Overview	PicoBlade™
Product Name	PicoBlade™

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Packaging Type	Bag
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.50-1.04mm
Wire Size AWG	26, 28
Wire Size mm²	N/A

Material Info

UPC 800753749740

Reference - Drawing Numbers

Product Specification PS-51021-001, PS-51021-002, PS-51021-009, PS-51021-010, PS-51021-011, PS-51021-022, PS-51021-023, PS-51021-024, PS-51021-025, PS-51021-026, PS-51021-027, PS-51021-028, RPS-501576-001, RPS-51021-001, RPS-51021-002, RPS-51021-003, RPS-51021-004, RPS-51021-006, RPS-51021-007, RPS-51021-008, RPS-51021-010, RPS-51021-011, RPS-51021-013, RPS-51021-014, RPS-51021-015, RPS-51021-016, RPS-51021-017, RPS-51021-018, RPS-51021-021, RPS-51021-023, RPS-51021-024, RPS-51021-025, RPS-51021-026, RPS-51021-027, RPS-51021-028, RPS-51021-029, RPS-51021-030, RPS-51021-031, RPS-51021-032, RPS-51021-033, RPS-51021-037, RPS-51021-038, RPS-51021-039, RPS-51021-040, RPS-51021-041, RPS-51021-043, RPS-51021-044, RPS-51021-045,

EU RoHS ELV and RoHS Compliant REACH SVHC Contains SVHC: No Low-Halogen Status Not Reviewed	China RoHS 
--	--

Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[50079Series](#)

Mates With

[50125](#) Crimp Terminal, [50133](#) Crimp Terminal

Use With

[51021](#) Crimp Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for 1.25mm Pitch Crimp Terminals, 26-32 AWG Wire	0638190300
Hand Crimp Tool for 1.25mm Pitch Crimp Terminals, 26-32 AWG Wire	0638190400

RPS-51021-046, RPS-51021-047, RPS-51021-048,
RPS-51021-050, RPS-51021-051, RPS-51021-052,
RPS-51021-053, RPS-51021-054, RPS-51021-055,
RPS-51021-056, RPS-51021-057, RPS-51021-058,
RPS-51021-059, RPS-51021-060, RPS-51021-061,
RPS-51021-062, RPS-51021-063, RPS-51021-064,
RPS-51021-065, RPS-51021-066, RPS-51021-067,
RPS-51021-068, RPS-51021-071, RPS-51021-072,
RPS-51021-073, RPS-51021-074, RPS-51021-076,
RPS-51021-077, RPS-51021-078, RPS-51021-079,
RPS-51021-081, RPS-51021-083, RPS-51021-084,
RPS-51021-085, RPS-51021-086, RPS-51021-089,
RPS-51021-091, RPS-51021-092, RPS-51021-096,
RPS-51021-097, RPS-51021-101, RPS-51021-102,
RPS-51021-103, RPS-51021-105, RPS-51021-106,
RPS-51021-107, RPS-51021-108, RPS-51021-112,
RPS-51021-113, RPS-53398-002, RPS-53398-037,
RPS-53398-038
SD-50079-001, SD-51021-002

Sales Drawing

Extraction Tool	<u>0011030043</u>
Japan	
Description	Product #
Hand Crimp Tool	<u>0571775000</u>
Extraction Tool	<u>0570726000</u>

This document was generated on 06/21/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION