

SPECIFICATIONS SHEET

PRODUCT TYPE : MAGNETIC TRANSDUCER

PRODUCT SERIES : 41.T70P015H-LF

COLOR : BLACK

ELECTRICAL SPECIFICATIONS

<u>MODEL NO.</u>	<u>41.T70P015H-LF</u>	
<u>OPERATING VOLTAGE RANGE</u>	(V)	1.0 ~ 5.0
<u>RATED VOLTAGE</u>	(V)	1.5
+ <u>MAX. RATED CURRENT</u>	(mA)	30.0
<u>COIL RESISTANCE</u>	(Ω)	16.0 +/- 4.5
<u>COIL IMPEDANCE</u>	(Ω)	40.0
+ <u>MIN. SOUND OUTPUT AT 10 cm</u>	(dBA)	85.0
<u>RESONANT FREQUENCY</u>	(Hz)	2048
<u>OPERATING TEMPERATURE</u>	(° C)	- 20 ~ + 60
<u>TERMINAL</u>		PIN
<u>HOUSING MATERIAL</u>		NORYL
<u>WEIGHT</u>	(g)	2.0

+ Value applying rated voltage resonant frequency, 1/2 duty , square wave

* Value applying resonant frequency, 1/2 duty , square wave ,measuring current 60uA

DIMENSIONS

UNIT : mm

