

SPECIFICATIONS SHEET

PRODUCT TYPE : MYLAR SPEAKER

PRODUCT SERIES : 41.MS36LS-LF

ELECTRICAL SPECIFICATIONS

<u>MODEL NO.</u>	<i>41.MS36LS-LF</i>	
<i>SHAPE</i>	ROUND	
<i>DIAMETER (D ± 0.3)</i>	mm	Ø 36.0
<i>HEIGHT (H ± 0.3)</i>	mm	6.5
<i>BACK DIA. (D ± 0.3)</i>	mm	Ø 17.0
<i>R. FREQUENCY ± 20 %</i>	Hz	500.0
<i>RESPONSE FREQ. F0 TO</i>	Hz	3.4 K
<i>RATED POWER</i>	W	0.15
<i>MAX POWER</i>	W	0.3
<i>STANDARD IMPEDANCE ± 15 % AT 1V</i>	Ω	8.0
<i>TERMINAL</i>	NIL	
<i>BUZZER & RATTLES</i>	1.095 V SINE WAVE	
<i>DISTORTION</i>	5.0% Max. (0.15 W 1.0 K Hz)	
<i>OPERATING TEMPERATURE</i>	°C	- 20.0 ~ + 55.0
<i>HOUSING MATERIAL</i>	METAL	
<i>DIAPHRAGM MATERIAL</i>	MYLAR	
<i>WEIGHT</i>	g	5.0 g

DIMENSIONS

UNIT : mm

TOP VIEW

SIDE VIEW

