

9007C68T10

LIMIT SWITCH 600V 10AMP C +OPTIONS



List Price \$266.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

Technical Characteristics

Operating Torque/Force	4 Inch-Pounds
Turret Head	Rotary Head (for Type C Lever Arms)
Plug-In Receptacle	Standard
Actuation	CW and CCW
Basic Switch (Plug-In Unit)	Standard
Actuator	Lever Arm (ordered separately)
Actuator Action	Spring Return - Standard Pretravel
Total Travel	90°
Differential Travel	4°
Approvals	UL Listed - CSA Certified - CE Marked
Pre-Travel	10°
Body Material	Zinc Alloy
Connection Type	0.5 Inch NPT Conduit Entrance (screw clamp terminals)
Contact Material	Silver Alloy
Contact Configuration	2 NO/2 NC (Neutral Position)
Contact Operation	Snap Action
Contact Rating	NEMA A600/R300
Ampere Rating	10A
Contact Form	Form ZZ - DPDT-DB
Operating Temperature Range	-20°F to 185°F
Maximum Voltage Rating	600V
Pilot Light	None
Type of Duty	Heavy Duty
Type	C

Shipping and Ordering

Category	21499 - Limit Switches, Heavy Duty, Type C
Discount Schedule	DS1
GTIN	00785901812098
Package Quantity	10
Weight	1.24 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y

Generated: 08/06/2012 07:24:52

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.