

9001KR9R

30MM PUSH-PULL OPERATOR RED KNOB

List Price \$129.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

Technical Characteristics

| | |
|-----------------------------|--|
| Approvals | UL File Number E42259 CCN NKCR - CSA File Number LR24590 Class 3211-03 - CE Marked |
| Bezel Material | Chromium Plated Metal |
| Button/Cap Color | Red |
| Button Type | Screw-On Plastic Mushroom (1.63 Inch/41mm) |
| Contact Configuration | No Contact Blocks |
| Guard Type | No Guard |
| Enclosure Type | Water tight, Dust tight and Oil tight (Indoor/Outdoor) |
| Enclosure Rating | NEMA 1/2/3/3R/4/6/12/13 |
| Head Type | Round |
| Light Module Supply Voltage | n/a |
| Light Module Type | n/a |
| Markings | None |
| Maximum Voltage Rating | 600V |
| Mounting Type | Panel |
| Number of Operators | 1 |
| Number of Positions | 2 |
| Operator Action | Maintained (Push/Pull) |
| Operator Type | Non-Illuminated |
| Size | 30mm |
| Type | K |

Shipping and Ordering

| | |
|-------------------|---|
| Category | 21426 - Push Buttons, 30 mm, Metal, Round, Type K |
| Discount Schedule | CS1 |
| GTIN | 00785901320128 |
| Package Quantity | 1 |
| Weight | 0.26 lbs. |
| Availability Code | Stock Item: This item is normally stocked in our distribution facility. |
| Returnability | Y |
| Country of Origin | MX |

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.