PNP SILICON PLANAR HIGH PERFORMANCE TRANSISTOR IN SOT223

Features

- BV_{CEO} > 60V
- Maximum continuous current $I_{C(cont)}$ = 3A
- Low Saturation Voltage
- Complementary Type – FZT651
- **Lead-Free Finish; RoHS compliant (Note 1)**
- **Halogen and Antimony Free. "Green" Device (Note 2)**
- **Qualified to AEC-Q101 Standards for High Reliability**

Mechanical Data

- Case: SOT223
- UL Flammability Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Matte Tin Finish
- Weight: 0.112 grams (approximate)

SOT223

Top View



Device Symbol



Top View
Pin-Out

Ordering Information (Notes 3 & 4)

Product	Grade	Marking	Reel size (inches)	Tape width (mm)	Quantity per reel
FZT751TA	Commercial	FZT751	7	12	1,000
FZT751QTA	Automotive	FZT751	7	12	1,000
FZT751TC	Commercial	FZT751	13	12	4,000
FZT751QTC	Automotive	FZT751	13	12	4,000

Notes:
1. EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant. All applicable RoHS exemptions applied.
2. Halogen and Antimony free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
3. For packaging details, go to our website at http://www.diodes.com.
4. Products with Q-suffix are automotive grade. Automotive products are electrical and thermal the same as the commercial, except where specified.

Marking Information



FZT751 = Product Type Marking Code

© Diodes Incorporated

Maximum Ratings @T_A = 25°C unless otherwise specified

Characteristic	Symbol	Value	Unit
Collector-Base Voltage	V_{CBO}	-80	V
Collector-Emitter Voltage	V_{CEO}	-60	V
Emitter-Base Voltage	V_{EBO}	-5	V
Continuous Collector Current	I_C	-3	A
Peak Pulse Current	I_{CM}	-6	A

Thermal Characteristics @T_A = 25°C unless otherwise specified

Characteristic		Symbol	Value	Unit
Power Dissipation	(Note 5)	P_D	2	W
	(Note 6)		3	W
Thermal Resistance, Junction to Ambient	(Note 5)	$R_{\theta JA}$	62.5	°C/W
	(Note 6)		41.7	°C/W
Thermal Resistance, Junction to Leads	(Note 7)	$R_{\theta JL}$	12.93	°C/W
Operating and Storage Temperature Range		T_J, T_{STG}	-55 to +150	°C

Notes:
5. For devices mounted on 25mm x 25mm single sided 2oz weight copper, in still air conditions.
6. For devices mounted on 50mm x 50mm single sided 2oz weight copper, in still air conditions.
7. Thermal resistance from junction to solder-point (at the end of the collector lead)

© Diodes Incorporated

Thermal Characteristics



Safe Operating Area



Safe Operating Area



Transient Thermal Impedance



Transient Thermal Impedance



Pulse Power Dissipation



Derating Curve

© Diodes Incorporated

Electrical Characteristics @T_A = 25°C unless otherwise specified

Characteristic	Symbol	Min	Typ	Max	Unit	Test Condition
Collector-Base Breakdown Voltage	BV_{CBO}	-80	–	–	V	I_C = -100µA
Collector-Emitter Breakdown Voltage (Note 8)	BV_{CEO}	-60	–	–	V	I_C = -10mA
Emitter-Base Breakdown Voltage	BV_{EBO}	-5	–	–	V	I_E = -100µA
Collector Cut-off Current	I_{CBO}	–	–	-0.1	µA	V_{CB} = -60V
		–	–	-10		V_{CB} = -60V, T_{amb} = 100°C
Emitter Cut-off Current	I_{EBO}	–	–	-0.1	µA	V_{EB} = -4V
Collector-Emitter Saturation Voltage (Note 8)	$V_{CE(sat)}$	–	-0.15	-0.3	V	I_C = -1A, I_B = -100mA
		–	-0.45	-0.6		I_C = -3A, I_B = -300mA
Base-Emitter Saturation Voltage (Note 8)	$V_{CE(sat)}$	–	-0.9	-1.25	V	I_C = -1A, I_B = -100mA
Base-Emitter Turn-On Voltage (Note 8)	$V_{BE(on)}$	–	-0.8	-1.0	V	I_C = -1A, V_{CE} = -2V
DC Current Gain (Note 8)	h_{FE}	70	200	–	–	I_C = -50mA, V_{CE} = -2V
		100	200	300		I_C = -500mA, V_{CE} = -2V
		80	170	–		I_C = -1A, V_{CE} = -2V
		40	150	–		I_C = -2A, V_{CE} = -2V
Current Gain-Bandwidth Product (Note 8)	f_T	100	140	–	MHz	V_{CE} = -5V, I_C = -100mA f = 100MHz
Turn-On Time	t_{on}	–	40	–	ns	V_{CC} = -10V, I_C = -500mA
Turn-Off Time	t_{off}	–	450	–	ns	I_{B1} = I_{B2} = -50mA
Output Capacitance (Note 8)	C_{obo}	–	–	30	pF	V_{CB} = -10V, f = 1MHz

Notes: 8. Measured under pulsed conditions. Pulse width ≤ 300 µs. Duty cycle ≤ 2%

© Diodes Incorporated

Typical Characteristics



VCE(sat) v IC



Switching Speeds



hFE v IC



VBE(sat) v IC



VBE(on) v IC

© Diodes Incorporated

Package Outline Dimensions



SOT223			
Dim	**Min**	**Max**	**Typ**
A	1.55	1.65	1.60
A1	0.010	0.15	0.05
b1	2.90	3.10	3.00
b2	0.60	0.80	0.70
C	0.20	0.30	0.25
D	6.45	6.55	6.50
E	3.45	3.55	3.50
E1	6.90	7.10	7.00
e	—	—	4.60
e1	—	—	2.30
L	0.85	1.05	0.95
Q	0.84	0.94	0.89
All Dimensions in mm			

Suggested Pad Layout



Dimensions	Value (in mm)
X1	3.3
X2	1.2
Y1	1.6
Y2	1.6
C1	6.4
C2	2.3

© Diodes Incorporated

IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

   1. are intended to implant into the body, or
   2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2012, Diodes Incorporated

www.diodes.com