

Cabtite KT 7 b**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Cabtite enables you to feed pre-assembled lines through the electrical cabinet wall while maintaining IP54-level protection. As the cable does not have to be split, the manufacturer's guarantee is not invalidated.

General ordering data

Order No.	1827840000
Type	Cabtite KT 7 b
Version	Cable grommet, Plastic
GTIN (EAN)	4032248333158
Qty.	10 pc(s).

Cabtite KT 7 b**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions**

Net weight	6.4 g
------------	-------

General information

Clamping range, bolted connection , max.	8 mm	Clamping range, min. test adapter	7 mm
Material	Plastic	Operating temperature range, max.	80 °C
Operating temperature range, min.	-20 °C		

Classifications

ETIM 2.0	EC000441	ETIM 3.0	EC000441
UNSPSC	30-21-18-01	eClass 4.1	27-14-12-96
eClass 5.1	27-14-92-01	eClass 6.0	27-14-92-01
eClass 7.0	27-14-92-01		

Approvals

Approvals