


P1,P2:	M-Y125A
	M-125A
P3:	M-487A

Customer No: No: 43



NOTE: All relevant materials are complied with RoHS directive .

	P1	P2
RED CONDUCTOR	1	1
RED SHIELD	6	6
GREEN CONDUCTOR	2	2
GREEN SHIELD	7	7
BLUE CONDUCTOR	3	3
BLUE SHIELD	8	8
BLACK	5	5
	10	10
WHITE	11	11
YELLOW	12	12
BROWN	13	13
ORANGE	14	14
SHIELD		SHIELD

No.	DESCRIPTION	Q'TY	Supplier
6	BLACK PVC TUBE $\phi 3.0 \times 22\text{mm}$	2	M304
	BLACK HEAT SHRINK TUPE $\phi 3.0 \times 10\text{mm}$	6	M743
	BLACK HEAT SHRINK TUPE $\phi 1.0 \times 6\text{mm}$	6	M959
	ALUMINUM FOIL 33*65mm	2	M579
	MOLDED PE COLOR TRANSPARENT		M280
	MOLDED PVC BEIGE		M304
5	UL2919 {[28AWG+AL+S(29/0.10mmTS)]*3COAXIAL+(30AWG*5C)};AL+D+AMA BRAID(47%),OD:7.5mm, JACKET BEIGE, DRAWING No.EAAB2803T3005C-195	L-20mm	M304
4	MOLDED THUMBSCREW #4-40 4.5*48mm, BEIGE	4	M95
3	HEX-NUT 5*6.6mm	2	M95
2	HD15 FEMALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	1	M108
1	HD15 MALE WITHOUT PIN 9, GOLD FLASH ON CONTACTS, BLUE INSULATOR	1	M108

APPROVED	CDEX-243	Cable Length Unless Other Spec. Tolerances: 0 ~200mm $\pm 10\text{mm}$ 201~1000mm $\pm 20\text{mm}$ 1001 ~1500mm $\pm 25\text{mm}$ 1501~2100mm $\pm 30\text{mm}$ 2100mm \uparrow $\pm 40\text{mm}$
CHECKED		
DRAWING		
DATE		
ITEM NO.		UNIT:mm