
Item no.: 280-832
Product description: 4-conductor through terminal block



Produkt kann von Bild abweichen / product may differ

Packing unit 100 pieces

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm ²]	0.08 - 2.5 mm ²
Cross section [AWG]	28 - 12 AWG
Connection method	CAGE CLAMP® CONNECTION
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	20 A
Weight	9.016 g
Color	yellow
Wiring type	Front-entry
No. of connection Points	4
No. of potentials	1
Height	28 mm
Height	1.1 in
Width	5 mm
Width	0.197 in
Depth	75 mm
Depth	2.95 in

Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in
Mounting	TS 35



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm²]
280-832	ABS	05-HG476175/3-PDA	800	20	2,5
280-832	BV	07436/Co	800	20	2,5
280-832	CCA	NL5855	800	24	2,5
280-832	CSA	154112-1536071	600	15	28-12
280-832	DNV	E-10423	800	20	2,5
280-832	GL	17295-00HH	800	24	2,5
280-832	KEMA	2082859.07	800	24	2,5
280-832	LR	91/20112(E6)	800	20	2,5
280-832	PRS	TE/1718/880590/08	800	24	2,5
280-832	RMR	11130002	800	20	2,5
280-832	UR	E45172	600	20	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected