




Inside mechanism



(1.6 Dimensions of P.C board holes
Printed-side view, Tolerance All±0.1
Type H=8

◇ Refer to attached sheet (detail of lead free solder plated) about lead free solder.

H=8



☆ Goods mass : About 2.3g

3	CENTER CONTACT	CNT61-0135N	1	BRASS	t0.5	(T)			LEAD FREE SOLDER PLATED
2	OUTER CONTACT	CNT71-0133	1	BRASS	t0.4	(S)			H6Cu2-Ni3 NICKEL PLATED
1	HOUSING	MOL41-5078A	1	PPHOX	RED			94HB	

TOLERANCE	X			
ALL under	±0.3	X		
over	±	X		
under	±	X		
over	±	X		
under	±	X		
ANGLE(DEG)	±3°	MARK		

ALL DIMENSIONS IN () ARE FOR REFERENCES ONLY				A · P	TITLE	PIN JACK	ISSUED
APPROVED	CHECKED	DRAWN	DESIGNED				
'95-4-18	'95-4-18	'95-4-18	'94-11-28	UNIT	mm	DRAWING No.	
				SCALE	2/1	PAGE	
				CUSTOMER CODE :		REVISION :	

Schurter Limited