

## 300 IP TORX PLUS® torque-indicator



**Application:** TORX PLUS® socket screws  
**Pre-set torque:** 0.6 Nm-3.0 Nm (0.4 ft.lb.-3.0 ft.lb.), fixed pre-sets  
**Accuracy:** ±10 %  
**Blade:** Hexagonal, 4 mm, reduced diameter tip  
**Design:** Black Point  
**Handle:** Kraftform with non-roll feature, multi-component

Code	Nm	ft. lb.	mm	mm	mm	mm	mm		
05028040001	6 IP	0.6	0.4	4	3.5	65	105	2 9/16"	1
05028041001	7 IP	0.9	0.7	4	3.5	65	105	2 9/16"	1
05028042001	8 IP	1.2	0.9	4	3.5	65	105	2 9/16"	1
05028043001	9 IP	1.4	1.0	4	3.5	65	105	2 9/16"	1
05028044001	10 IP	2.0	1.5	4	3.8	65	105	2 9/16"	1
05028045001	15 IP	3.0	2.2	4	3.8	65	105	2 9/16"	1