









300 IP Drehmomentindikator TORX PLUS®



Anwendung: Innen-TORX PLUS®-Schrauben
Messwert: 0,6 Nm-3,0 Nm (0.4 ft.lb.-3.0 ft.lb.), fest voreingestellt
Präzision: ± 10 %
Klinge: Sechskant, 4 mm, überdreht
Ausführung: Black Point Spitze
Griff: Kraftform mit Abrollschutz, mehrkomponentig

									
Code		Nm	ft. lb.	mm	mm	mm	mm	mm	
05028040001	6 IP	0,6	0,4	4	3,5	65	105	2 9/16"	1
05028041001	7 IP	0,9	0,7	4	3,5	65	105	2 9/16"	1
05028042001	8 IP	1,2	0,9	4	3,5	65	105	2 9/16"	1
05028043001	9 IP	1,4	1,0	4	3,5	65	105	2 9/16"	1
05028044001	10 IP	2,0	1,5	4	3,8	65	105	2 9/16"	1
05028045001	15 IP	3,0	2,2	4	3,8	65	105	2 9/16"	1