

300 TX Drehmomentindikator TORX®



Anwendung: Innen-TORX®-Schrauben
Messwert: 0,6 Nm-3,0 Nm (0.4 ft.lb.-2.2 ft.lb.), fest voreingestellt
Präzision: ± 10 %
Klinge: Sechskant, 4 mm, überdreht
Ausführung: Black Point Spitze
Griff: Kraftform mit Abrollschutz, mehrkomponentig

Code		Nm	ft. lb.	mm	mm	mm	mm		
05027930001	TX 6	0,6	0,4	4	3,5	65	105	2 9/16"	1
05027931001	TX 7	0,9	0,7	4	3,5	65	105	2 9/16"	1
05027932001	TX 8	1,2	0,9	4	3,5	65	105	2 9/16"	1
05027933001	TX 9	1,4	1,0	4	3,5	65	105	2 9/16"	1
05027934001	TX 10	2,0	1,5	4	3,8	65	105	2 9/16"	1
05027935001	TX 15	3,0	2,2	4	3,8	65	105	2 9/16"	1