

_			1		2 3				4	5		6
	APPLICATION SPECIFIC				APF	PLICATION	SPECIFIC		APPLICATION S	PECIFIC		
	PIN STYLE	MATING	SOLDER	OAL	PIN STYLE	MATING	SOLDER	OAL	PIN STYLE MATING S	SOLDER OAL		
	01	5.72	2.54	10.8	27	6.6	2.67	11.81	97 7.75	3.05 13.34		
	02	5.84	3.43	11.81	28	6.6	4.19	13.34	98 10.29	3.05 15.88		
	03	5.72	5.09	13.34	29	17.53	3.43	23.5				
	04	5.72	7.62	15.88	30	22.61	3.43	28.58				
	05	5.72	10.16	18.42	31	8.2	2,84	13.59			2.4	
	06	5.72	12.7	20.96	32	10.29	3.05	15.88				
	07	5.72	15.24	235	35	25.21	3.37	31.12		\$\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\	□	
Δ	08	5.72	17.78	26.04	38	5 <i>.</i> 84	3.81	12.19				
	09	5.72	20.32	28.58	39	11.17	3.05	16.76	(N	N x 2.54 OTE 6 SHEET 1)	'	
	10	5.72	22.86	31.12	41	4.99	2.8	10.33		OIE O SHEEL I)		
	11	5.72	5.97	14.22	43	6.98	4.8	14.32	1 00+0 1	p (いつ)		
	12	5.72	8.51	16.76	44	12.27	3.35	18 <i>.</i> 16	1.09±0.18	o (x2)		
	13	5.72	11.05	19.3	46	8.08	2.72	13.34		4 4 4	<u></u>	
	14	5.72	16.13	24.38	48	5.84	2.42	10.8			\Box	
	15	8.51	2.54	13.59	50	5.84	3.12	11.5			2.54	
	16	8.51	5.51	16.56	56	5.72	3.05	11.3				
	17	8.51	10.59	21.64	61	16.61	3.2	22.35	 			
-	18	5.72	3.05	11.3	62	13.5	3.05	19.09			<u></u>	
	19	12.83	3.05	18.42	70	6.54	3.5	12.57			0.2	
2	20	15.37	3.05	20.96	73	28.4	3.18	34.12	$egin{array}{cccccccccccccccccccccccccccccccccccc$		\coprod	
	21	20.45	3.05	26.04	75	16.47	10.3	29.31		T T T	Υ	
-	22	7 <i>.</i> 75	3.05	13.34	79	3.3	3.3	9.14		ESIGN AND DIMENSIONS		
	23	5.84	4.95	13.34	80	8.07	2.2	12.81	ONLY FOR	R FOLLOWING P/NUMBE	-R :	
	24	7.21	3.05	12.8	90	1.9	3.56	8	75160-101/301->	(X(LF); 75160-102-XX	((LF)	
	25	8.51	3.18	14.22	95	15.96	4	22.5		(X(LF) ; 75160—322—)	·	
	26	15.57	2.84	20.96	96	5.84	3.43	11.81	75160-132-XX(LF)	•	,,,(_,)	
										,		
												,
										rance projection product far	nily BERGSTIK	
									SEE P/N ISO 1302 V ISO 40 Ltr ecn no dr date tolerances unless otherw		DENGSTIK	
									BH -05-0186 JCO 05.04.29 BJ -06-0196 LMU 06.06.20 Linear .xx :		DER STR,	.SR.
									xxx	±0.05 scale 5:1 2.5	4mm PITCH	•
										99.04.07 FC) dwg no	sheet 2 of	
									BF F20607 LM 03.12.03 chr	/	75160	<u>A</u> 3
									BC F03079 LMU 03.04.04 appd JMC sheet revision	99.04.07 type C	USTOMER Dr	rawing
									index sheet			
	EA :mro		1		2		3	3	4	5 l		6