

2 Drive 2.5in Trayless Hot Swap SATA Mobile Rack Backplane

StarTech ID: HSB220SAT25B



This 3.5in SATA hard drive hot-swap bay allows you to install two 2.5in SATA (SATA, SATA II, SATA III-6Gbps) hard drives (HDD) or solid state drives (SSD) in an available/unused 3.5in floppy drive bay.

Featuring a convenient "no mounting required /easy eject" feature (like a tape cartridge or floppy disk), the hard drive hot swap bay doesn't require that the drives be installed in a tray - making it the ideal solution for quick and easy drive removals and insertions as part of a system building process, or integration into rackmount systems or industrial environments.

Also a perfect addition for operating system image deployment and any task that requires being able to quickly access large volumes of data on the fly, the hot swap bay provides everything you need to expedite important projects while maintaining a reliable storage solution.

With support for SATA HDD speeds up to 6.0 Gbps, this backplane is fully compatible with RAID installations to ensure maximum performance and versatility for enhanced storage applications.

Applications

- IT environments where you just need to quickly insert/replace removable hard drives/solid state drives
- Imaging - For System Builders or configuring new systems - Use Hot Swap Bay in master system to copy Windows OS quickly to blank hard drive as part of system building process
- Ideal for RAID applications (with RAID supported SATA controller)

Features

- Holds up to two SATA drives in a single 3.5" bay
- Trayless design: drives are not mounted into separate trays/enclosures
- Includes a plastic protective film for the bottom side of hard drive
- Aluminum construction
- 50,000+ insertion rating
- Power/Activity LED for each drive
- Fully supports SATA revision 1/2/3 (1.5/3.0/6.0 Gbps) drives and controllers
- Supports 2.5" form factor SATA hard drives (HDD) and solid state drives (SSD)
- Plug-and-Play and Hot-Swap compatible

Technical Specifications

Warranty	2 Years
Key Lock	No
Number of Drives	2
Drive Size	2.5in
Drive Type	SATA
Connector Type(s)	2 - SATA (7 pin; Data) Receptacle
Connector Type(s)	2 - SATA Power (15 pin) Receptacle
Connector Type(s)	2 - SP4 (4 pin; Small Drive Power) Male
Drive Connectors	2 - SATA (7 pin; Data) Receptacle
Drive Connectors	2 - SATA Power (15 pin) Receptacle
Host Connectors	2 - SATA (7 pin; Data) Plug
Host Connectors	2 - SATA Power (15 pin) Plug
Type and Rate	SATA III (6 Gbps)
Max Drive Capacity	Tested up to 500GB per drive
Hot Swap Capability	Yes
Color	Black
Enclosure Type	Aluminum
Max Drive Height	9.5 mm [0.4 in]
Product Length	134 mm [5.3 in]
Product Width	102 mm [4 in]
Product Height	24 mm [0.9 in]
Product Weight	282.5 g [10 oz]
LED Indicators	1 - Power/Drive Activity
Shipping (Package) Weight	0.5 kg [1.1 lb]
Included in Package	1 - Dual SATA Hot-Swap Bay
Included in Package	2 - LP4-to-4-pin LED/15-pin SATA Power Y-cable
Included in Package	2 - SATA Cable
Included in Package	2 - Hard Drive Protector Film
Included in Package	1 - Screw Kit
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

