



No-Clean Desoldering Braid

Desoldering Braid
1814-1825, 1827, 1829

Introduction

Techspray's No-Clean Desoldering Braid has changed the perception of desoldering braids. It removes up to four times more solder than the conventional wick, and extracts the solder much, much faster than wicks based on Type R fluxes and outperforms competitors' no-clean braid. This flux improves the wicking action. The residue left behind is halide free and non-conductive so it does not have to be cleaned off the board! The No-Clean Desoldering Braid is designed to improve reworking efficiency in both conventional and no-clean operations.

Features / Benefits

No-Clean Flux

Advanced Braid Design

Vacuum Packed

Anti-Static Bobbin (1820-1825, 1827, 1829) are within 10^5 to 10^{11} ohms resistivity

Chemical Components

Non-ionic flux mixture

<5%

Environmental Policy

Techspray® is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Packaging and Availability

No-Clean Desoldering Braid is available in the following sizes:

1814-1818	5F, 10F, 25F, 50F, 100F, 500F
1819	5F, 25F, 50F, 100F, 500F
1820-1823	5F, 10F, 25F, 50F, 100F
1824	5F, 10F, 25F
1825	5F, 25F
1827	5F, 10F
1829	5F

Resources

Techspray® products are supported by global sales, technical and customer services resources.

For additional technical information on this product or other Techspray® products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

North America
Tech Spray L.P.
P.O. Box 949
Amarillo, TX 79105
800-858-4043
email: tsales@techspray.com

Europe
Techspray International
UNIT 4, 44/46 Bunyan Road, Kempston
Bedford MK42 8HL United Kingdom
+44 (0) 1234 855443
email: tseurope@techspray.com

Countries Outside US
Call to locate a distributor
in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray® be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.



Tech Spray, L.P.
P.O. Box 949
Amarillo, TX 79105
www.techspray.com

[English MSDS](#)
[French MSDS](#)
[German MSDS](#)
[Italian MSDS](#)
[Spanish MSDS](#)

