

1½ tons of grip that weighs less than 3 pounds!

### Battery-Powered Crimping Tool — BAT22-6

T&B's newest battery-powered tool is fast and portable for making high-volume and difficult-to-reach terminal installations in a snap. The Sta-Kon® BAT22-6 delivers 1.5 tons of crimping force with an easy, pushbutton trigger. The lightweight, ergonomic design minimizes the risk of repetitive motion injuries that can occur with traditional hand crimping tools. And at less than three pounds, one-hand operation is easy while still packing enough power to crimp up to 6 AWG terminals in seconds.

- Interchangeable dies can be quickly changed to crimp non-insulated and insulated terminals up to 6 AWG
- Dies are the same as our hand tools — crimps will be exactly the same between Sta-Kon® hand tools such as our ERG2001 and the new BAT22-6
- 360° rotating head gives the user the added flexibility when crimping hard-to-reach connections
- Short cycle time equates to crimping times of less than two seconds
- Quick, lightweight, and maneuverable
- NiCd battery operation provides long-lasting battery life to complete up to 150 crimps on a single charge
- Extra battery and charger are included with the tool, ensuring round-the-clock operation
- Battery charger provides full battery life in under an hour
- Linear crimping motion gives a symmetric, high-quality crimp every time



Easy to rotate with your wrist — delivers fast and effective crimping power.



**NEW!**

Uses the exact dies of the Comfort Crimp line of ergonomic tools for Sta-Kon® and Dragon Tooth® terminals.

#### Included Accessories

- Sturdy, plastic carrying case for portability
- Two 9.6V NiCd batteries and battery charger
- Sturdy tray for convenient storage of crimp dies

| CAT. NO.           | DESCRIPTION   | PKG. QTY. |
|--------------------|---|-----------|
| BAT22-6            | Battery Crimping Tool, 1.5 Ton with 120 VAC Charger | 1         |
| <b>Crimp Dies*</b> |   |           |
| DIE2001            | Insulated 22–10 AWG Sta-Kon Terminals               | 1         |
| DIE2002            | Non-Insulated 22–10 AWG Sta-Kon Terminals           | 1         |
| DIE2005            | 16–14/12–10/8–6 (Tubular Only) Sta Kon Terminals    | 1         |
| DIE2007            | Insulated 8–6 AWG Sta-Kon Terminals                 | 1         |

\*Dies sold separately.