

Normal Wall Flame Retardant Heat Shrink Tubing

pro-POWER

Features:

- Flexible, general purpose, polyolefin tubing
- 2:1 shrink ratio
- Super abrasion and solvent resistance
- Excellent physical, chemical and electrical properties
- Wide range of sizes and colours
- Operating temperature range : -55°C to 125°C



Specifications:

Physical:

Tensile Strength	: 14.8 Mpa
Elongation	: 460%
Tensile Strength After Aging	: 14.5Mpa
Elongation After Aging	: 480%

Electrical:

Dielectric Strength	: 17 KV / mm
Volume Resistance	: $1 \times 10^{15} \Omega \text{ cm}$

Chemical:

Corrosion UL 224 (158C × 168 hours) Pass;
Copper Stability UL 224 (158C × 168 hours) Pass

Normal Wall Flame Retardant Heat Shrink Tubing



Specification Table

Size (Inch)	Inside Diameter		Recovered Wall Thickness
	As Supplied	Maximum After Recovery	
3/64	1 ±0.2	0.5	0.22 ±0.1
1/16	1.5 ±0.3	0.65	0.28 ±0.1
3/32	2.5 ±0.3	1	0.35 ±0.1
1/8	3.5 ±0.4	1.5	0.4 ±0.1
3/16	5 ±0.4	2.3	0.5 ±0.1
1/4	6.5 ±0.4	3	0.55 ±0.1
3/8	9.5 ±0.5	4.5	0.6 ±0.1
1/2	12.5 ±0.5	6	
3/4	19 ±0.7	9	0.8 ±0.15
1	26 ±0.7	12.5	0.9 ±0.15
1-1/4	29 ±0.7	14	
1-1/2	41.5 ±0.7	20	1 ±0.15
2	51 ±0.7	25	
3	≥80	41	1.46 ±0.2
4	≥100	51	

Dimensions : Millimetres

Part Number Table

Description	Part Number	Description	Part Number
Heat Shrink Tubing 2:1 Black 1.6 mm 100 M	13633	Heat Shrink Tubing 2:1 Black 6.4 mm 5 M	13648
Heat Shrink Tubing 2:1 Black 2.4 mm 100 M	13634	Heat Shrink Tubing 2:1 Black 9.5 mm 5 M	13649
Heat Shrink Tubing 2:1 Black 3.2 mm 100 M	13635	Heat Shrink Tubing 2:1 Black 12.7 mm 5 M	13650
Heat Shrink Tubing 2:1 Black 4.8 mm 100 M	13636	Heat Shrink Tubing 2:1 Black 19 mm 5 M	13651
Heat Shrink Tubing 2:1 Black 6.4 mm 100 M	13637	Heat Shrink Tubing 2:1 Black 25.4 mm 5 M	13652
Heat Shrink Tubing 2:1 Black 9.5 mm 100 M	13638	Heat Shrink Tubing 2:1 Black 38.1 mm 5 M	13653
Heat Shrink Tubing 2:1 Black 12.7 mm 100 M	13639	Heat Shrink Tubing 2:1 Black 50.8 mm 5 M	13654
Heat Shrink Tubing 2:1 Black 19 mm 100 M	13640	Heat Shrink Tubing 2:1 Clear 1.6 mm 100 M	13655
Heat Shrink Tubing 2:1 Black 25.4 mm 50 M	13641	Heat Shrink Tubing 2:1 Clear 2.4 mm 100 M	13656
Heat Shrink Tubing 2:1 Black 38.1 mm 50 M	13642	Heat Shrink Tubing 2:1 Clear 3.2 mm 100 M	13657
Heat Shrink Tubing 2:1 Black 50.8 mm 25M	13643	Heat Shrink Tubing 2:1 Clear 4.8 mm 100 M	13658
Heat Shrink Tubing 2:1 Black 1.6 mm 5 M	13644	Heat Shrink Tubing 2:1 Clear 6.4 mm 100 M	13659
Heat Shrink Tubing 2:1 Black 2.4 mm 5 M	13645	Heat Shrink Tubing 2:1 Clear 9.5 mm 100 M	13660
Heat Shrink Tubing 2:1 Black 3.2 mm 5 M	13646	Heat Shrink Tubing 2:1 Clear 12.7 mm 100 M	13661
Heat Shrink Tubing 2:1 Black 4.8 mm 5 M	13647	Heat Shrink Tubing 2:1 Clear 19 mm 100 M	13662

Normal Wall Flame Retardant



Heat Shrink Tubing

Part Number Table

Description	Part Number
Heat Shrink Tubing 2:1 Clear 25.4 mm 50 m	13663
Heat Shrink Tubing 2:1 Clear 38.1 mm 50 m	13664
Heat Shrink Tubing 2:1 Clear 50.8 mm 25 m	13665
Heat Shrink Tubing 2:1 Clear 1.6 mm 5 m	15034
Heat Shrink Tubing 2:1 Clear 2.4 mm 5 m	15035
Heat Shrink Tubing 2:1 Clear 3.2 mm 5 m	15036
Heat Shrink Tubing 2:1 Clear 4.8 mm 5 m	15037
Heat Shrink Tubing 2:1 Clear 6.4 mm 5 m	15038
Heat Shrink Tubing 2:1 Clear 9.5 mm 5 m	15039
Heat Shrink Tubing 2:1 Clear 12.7 mm 5 m	15040
Heat Shrink Tubing 2:1 Clear 19 mm 5 m	15041
Heat Shrink Tubing 2:1 Clear 25.4 mm 5 m	15042
Heat Shrink Tubing 2:1 Clear 50.8 mm 5 m	15044
Heat Shrink Tubing 2:1 Red 1.6 mm 100 m	13666
Heat Shrink Tubing 2:1 Red 2.4 mm 100 m	13667
Heat Shrink Tubing 2:1 Red 3.2 mm 100 m	13668
Heat Shrink Tubing 2:1 Red 4.8 mm 100 m	13669
Heat Shrink Tubing 2:1 Red 6.4 mm 100 m	13670
Heat Shrink Tubing 2:1 Red 9.5 mm 100 m	13671
Heat Shrink Tubing 2:1 Red 12.7 mm 100 m	13672
Heat Shrink Tubing 2:1 Red 19 mm 100 m	13673
Heat Shrink Tubing 2:1 Red 25.4 mm 50 m	13674
Heat Shrink Tubing 2:1 Red 38.1 mm 50 m	13675
Heat Shrink Tubing 2:1 Red 1.6 mm 5 m	15045
Heat Shrink Tubing 2:1 Red 2.4 mm 5 m	15046
Heat Shrink Tubing 2:1 Red 3.2 mm 5 m	15047
Heat Shrink Tubing 2:1 Red 4.8 mm 5 m	15048
Heat Shrink Tubing 2:1 Red 6.4 mm 5 m	15049
Heat Shrink Tubing 2:1 Red 9.5 mm 5 m	15050
Heat Shrink Tubing 2:1 Red 12.7 mm 5 m	15051
Heat Shrink Tubing 2:1 Red 19 mm 5 m	15052
Heat Shrink Tubing 2:1 Red 25.4 mm 5 m	15053
Heat Shrink Tubing 2:1 Red 38.1 mm 5 m	15054
Heat Shrink Tubing 2:1 Yellow 2.4 mm 100 m	13678

Description	Part Number
Heat Shrink Tubing 2:1 Yellow 3.2 mm 100 m	13679
Heat Shrink Tubing 2:1 Yellow 4.8 mm 100 m	13680
Heat Shrink Tubing 2:1 Yellow 6.4 mm 100 m	13681
Heat Shrink Tubing 2:1 Yellow 9.5 mm 100 m	13682
Heat Shrink Tubing 2:1 Yellow 12.7 mm 100 m	13683
Heat Shrink Tubing 2:1 Yellow 19 mm 100 m	13684
Heat Shrink Tubing 2:1 Yellow 25.4 mm 50 m	13685
Heat Shrink Tubing 2:1 Yellow 50.8 mm 25 m	13687
Heat Shrink Tubing 2:1 Yellow 1.6 mm 5 m	15056
Heat Shrink Tubing 2:1 Yellow 2.4 mm 5 m	15057
Heat Shrink Tubing 2:1 Yellow 3.2 mm 5 m	15058
Heat Shrink Tubing 2:1 Yellow 4.8 mm 5 m	15059
Heat Shrink Tubing 2:1 Yellow 6.4 mm 5 m	15060
Heat Shrink Tubing 2:1 Yellow 9.5 mm 5 m	15061
Heat Shrink Tubing 2:1 Yellow 12.7 mm 5 m	15062
Heat Shrink Tubing 2:1 Yellow 19 mm 5 m	15063
Heat Shrink Tubing 2:1 Yellow 25.4 mm 5 m	15064
Heat Shrink Tubing 2:1 Yellow 38.1 mm 5 m	15065
Heat Shrink Tubing 2:1 White 1.6 mm 100 m	13688
Heat Shrink Tubing 2:1 White 2.4 mm 100 m	13689
Heat Shrink Tubing 2:1 White 3.2 mm 100 m	13690
Heat Shrink Tubing 2:1 White 4.8 mm 100 m	13691
Heat Shrink Tubing 2:1 White 6.4 mm 100 m	13692
Heat Shrink Tubing 2:1 White 9.5 mm 100 m	13693
Heat Shrink Tubing 2:1 White 12.7 mm 100 m	13694
Heat Shrink Tubing 2:1 White 38.1 mm 50 m	13697
Heat Shrink Tubing 2:1 White 1.6 mm 5 m	15067
Heat Shrink Tubing 2:1 White 2.4 mm 5 m	15068
Heat Shrink Tubing 2:1 White 3.2 mm 5 m	15069
Heat Shrink Tubing 2:1 White 4.8 mm 5 m	15070
Heat Shrink Tubing 2:1 White 6.4 mm 5 m	15071
Heat Shrink Tubing 2:1 White 9.5 mm 5 m	15072
Heat Shrink Tubing 2:1 White 12.7 mm 5 m	15073
Heat Shrink Tubing 2:1 White 25.4 mm 5 m	15075

Normal Wall Flame Retardant Heat Shrink Tubing

pro-POWER

Part Number Table

Description	Part Number
Heat Shrink Tubing 2:1 White 38.1 mm 5 m	15076
Heat Shrink Tubing 2:1 White 50.8 mm 5 m	15077
Heat Shrink Tubing 2:1 Blue 1.6 mm 100 m	13699
Heat Shrink Tubing 2:1 Blue 2.4 mm 100 m	13700
Heat Shrink Tubing 2:1 Blue 3.2 mm 100 m	13701
Heat Shrink Tubing 2:1 Blue 4.8 mm 100 m	13702
Heat Shrink Tubing 2:1 Blue 6.4 mm 100 m	13703
Heat Shrink Tubing 2:1 Blue 9.5 mm 100 m	13704
Heat Shrink Tubing 2:1 Blue 12.7 mm 100 m	13705
Heat Shrink Tubing 2:1 Blue 25.4 mm 50 m	13707
Heat Shrink Tubing 2:1 Blue 1.6 mm 5 m	15078
Heat Shrink Tubing 2:1 Blue 2.4 mm 5 m	15079
Heat Shrink Tubing 2:1 Blue 3.2 mm 5 m	15080
Heat Shrink Tubing 2:1 Blue 4.8 mm 5 m	15081
Heat Shrink Tubing 2:1 Blue 6.4 mm 5 m	15082
Heat Shrink Tubing 2:1 Blue 9.5 mm 5 m	15083
Heat Shrink Tubing 2:1 Blue 12.7 mm 5 m	15084
Heat Shrink Tubing 2:1 Blue 19 mm 5 m	15085
Heat Shrink Tubing 2:1 Blue 25.4 mm 5 m	15086
Heat Shrink Tubing 2:1 Blue 38.1 mm 5 m	15087
Heat Shrink Tubing 2:1 Blue 50.8 mm 5 m	15088
Heat Shrink Tubing 2:1 Green / Yellow 1.6 mm 100 m	13710
Heat Shrink Tubing 2:1 Green / Yellow 2.4 mm 100 m	13711
Heat Shrink Tubing 2:1 Green / Yellow 3.2 mm 100 m	13712
Heat Shrink Tubing 2:1 Green / Yellow 4.8 mm 100 m	13713
Heat Shrink Tubing 2:1 Green / Yellow 6.4 mm 100 m	13714
Heat Shrink Tubing 2:1 Green / Yellow 9.5 mm 100 m	13715
Heat Shrink Tubing 2:1 Green / Yellow 12.7 mm 100 m	13716
Heat Shrink Tubing 2:1 Green / Yellow 19 mm 100 m	13717
Heat Shrink Tubing 2:1 Green / Yellow 25.4 mm 50 m	13718
Heat Shrink Tubing 2:1 Green / Yellow 38.1 mm 50 m	13719
Heat Shrink Tubing 2:1 Green / Yellow 1.6 mm 5 m	15089
Heat Shrink Tubing 2:1 Green / Yellow 2.4 mm 5 m	15090
Heat Shrink Tubing 2:1 Green / Yellow 3.2 mm 5 m	15091

Normal Wall Flame Retardant Heat Shrink Tubing



Part Number Table

Description	Part Number
Heat Shrink Tubing 2:1 Green / Yellow 4.8 mm 5 m	15092
Heat Shrink Tubing 2:1 Green / Yellow 6.4 mm 5 m	15093
Heat Shrink Tubing 2:1 Green / Yellow 9.5 mm 5 m	15094
Heat Shrink Tubing 2:1 Green / Yellow 12.7 mm 5 m	15095
Heat Shrink Tubing 2:1 Green / Yellow 19 mm 5 m	15096
Heat Shrink Tubing 2:1 Green / Yellow 38.1 mm 5 m	15098
Heat Shrink Tubing 2:1 Green / Yellow 50.8 mm 5 m	15099
Heat Shrink Tubing 2:1 Brown 1.6 mm 100 m	13721
Heat Shrink Tubing 2:1 Brown 2.4 mm 100 m	13722
Heat Shrink Tubing 2:1 Brown 3.2 mm 100 m	13723
Heat Shrink Tubing 2:1 Brown 6.4 mm 100 m	13725
Heat Shrink Tubing 2:1 Brown 25.4 mm 50 m	13729
Heat Shrink Tubing 2:1 Brown 38.1 mm 50 m	13730
Heat Shrink Tubing 2:1 Brown 50.8 mm 25 m	13731
Heat Shrink Tubing 2:1 Brown 1.6 mm 5 m	15100
Heat Shrink Tubing 2:1 Brown 2.4 mm 5 m	15101
Heat Shrink Tubing 2:1 Brown 3.2 mm 5 m	15102
Heat Shrink Tubing 2:1 Brown 4.8 mm 5 m	15103
Heat Shrink Tubing 2:1 Brown 6.4 mm 5 m	15104
Heat Shrink Tubing 2:1 Brown 9.5 mm 5 m	15105
Heat Shrink Tubing 2:1 Brown 12.7 mm 5 m	15106
Heat Shrink Tubing 2:1 Brown 19 mm 5 m	15107
Heat Shrink Tubing 2:1 Brown 25.4 mm 5 m	15108
Heat Shrink Tubing 2:1 Brown 38.1 mm 5 m	15109
Heat Shrink Tubing 2:1 Brown 50.8 mm 5 m	15110

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.