

Switched Socket



Specification Table

Material	Metalclad	
Connector Type	UK Mains	Twin UK Mains
Pin Format	UK Mains	
Supply Voltage (V ac)	250	
Voltage Rating (V ac)	250	
Current Rating (A)	13	
Length	80	145
External Length / Height	80	
External Width	40	
Fixing Centres	60	120
Fixing Hole Diameter	4	
Number of Outputs	1	2
Approval Category	BS1363	
Part Number	9499SMB	9498SMB

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Pro-ELEC is the registered trademark of the Group. © Premier Farnell plc 2012.