



REVISIONS			
ZONE	REV	DESCRIPTION	DATE
APPROVED			


FRONT VIEW – COVER OPEN 180 DEG.




RIGHT SIDE VIEW




FRONT VIEW



END VIEW



SECTION A-A VIEW



- NOTES:
1. ENCLOSURE MATERIAL MADE OF BEIGE (RAL 7032) HOT MOLDED FIBERGLASS REINFORCED POLYESTER.
 2. UL LISTED PER STD. 508.
 3. CSA CERTIFIED PER STD. C22.2 NO. 94.
 4. NEMA RATED TYPE 3, 3R, 3S, 4, 4X, 12 AND 13.
 5. IEC SP2 RATED IP 66-11.
 6. RESISTANT TO TEMPERATURES UP TO 150 DEG C.
 7. SELF EXTINGUISHING AND HALOGEN FREE.
 8. ACCESSORIES INCLUDE: BACK PANELS, HINGEABLE POLYESTER FRONT PLATES, DIN RAIL MOUNTING SYSTEM, PRINT POCKET, LOCKING HANDLES, AND VENTILATORS.
 9. CABINETS ARE MAINTENANCE FREE AND CORROSION RESISTANT.

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE IN INCHES AND DECIMALS THEREOF.		VYNCKIER ENCLOSURE SYSTEMS, INC.	
DRAWN BY: J. B. BROWN		ARIA ENCLOSURE SERIES	
CHECKED BY: J. B. BROWN		VYNCKIER PART # ANB2016PL	
DATE: 10/20/20		SCALE: FULL	
DESIGN: J. B. BROWN		SHEET: 0	