

VIBTEC

ELECTRIC VIBRATORS Series MVSI - S90

Farnell Reference	Model - S90	Category	Frame Size	CF KGS	Power W	Curr A	A	B	C	D	E	F	Dia G	H	Wt KGS
7035299	MVSI 3 / 100 - S90	3000 RPM 380 / 415V 3PH 50Hz	00	100	180	0.35	210	141	125	62 / 74	106	15	9	55	4.30
7035305	MVSI 3 / 200 - S90		01	193	180	0.35	220	151	125	62 / 74	106	24	9	64	4.95
7035317	MVSI 3 / 300 - S90		10	304	260	0.60	245	181	152	90	125	29.50	13	73	8.25
7035329	MVSI 3 / 500 - S90		20	503	450	0.80	277	198	167	105	140	28.50	13	80	12.45
7035147	MVSI 3 / 100 - S90	3000 RPM 220 / 240V 1PH 50Hz	00	100	165	0.75	210	141	125	62 / 74	106	15	9	55	4.30
7035159	MVSI 3 / 200 - S90		01	193	165	0.75	220	151	125	62 / 74	106	24	9	64	4.95
7035160	MVSI 3 / 300 - S90		10	304	280	1.25	245	181	152	90	125	29.50	13	73	8.25
7035172	MVSI 3 / 500 - S90		20	503	500	2.30	277	198	167	105	140	28.50	13	80	12.45

