

SUPERB SPEED. EVERYDAY CONVENIENCE.

Introducing the Dell™ V313 and V313w All-In-One Printers.

Experience convenience, speed and efficiency with the Dell™ V313 and V313w All-In-One Printers. The Dell V313w comes with integrated wireless* capabilities so you can print professional-looking pieces from anywhere in your home or office – without cables. Cutting-edge technology now provides a faster printer than the previous generation with outstanding grain and banding quality using various types of paper.

Equipped with convenient features, the Dell V313 and V313w give you three functions in a sleek desktop design. From monochrome and color printing to copying and scanning, these versatile printers offer fast print speeds and brilliant results at a very smart price. Built-in Eco-Mode complements the feature set and increases energy savings by dimming the LCD display after 2 minutes and going into Power Saver mode after 10 minutes.

Get the maximum value you deserve with a printing package that combines proven performance, sleek and intuitive design, and high-quality service and support.



Dell V313 and V313w All-In-One Printers
Wireless model: Dell V313w All-In-One Printer

Exceptional Performance

- Integrated Wi-Fi® 802.11b/g on V313w
- Versatile printing, copying and scanning
- Vivid colors and enhanced graphics enabled up to 1200x2400 dpi print resolution
- Fast monochrome ink printing up to 33ppm and color ink printing up to 30ppm (actual print speed will vary with use)
- Fast monochrome copying up to 25ppm and color copying up to 21ppm (actual copy speed will vary with use)

Easy To Use

- Experience energy savings with Eco-Mode which enables dimming of LCD after 2 minutes and goes to Power Saver mode after 10 minutes
- Print photos without your PC via memory cards, PictBridge™ and USB memory devices
- Quick plug-and-play setup with pre-installed drivers, when ordered in conjunction with a Dell system
- Fast and easy ink installation and replacement

Earth-Friendly

- Energy Star®-compliant
- Dell Recycling Program: for printer and ink

To learn more about how Dell is putting eco-friendly responsibility into action, visit DELL.COM/Recycling

The Dell Ink Advantage

Dell Ink Management System: EASY AS 1-2-3

1. Intelligent software alerts you when ink levels are low.
2. Click "Order Ink Online" and connect directly to DELL.COM/Supplies and www.premier.dell.com or call 1-877-ink-2-you.
3. Save time and money with free 3-5 day shipping.¹

Easy Ordering: Simply place your order online, or by phone and Dell's world-class global supply chain will send a replacement cartridge direct to your door. Cartridges are also available at many retail locations.*

Reliable: Genuine Dell Ink helps give you optimal results with every print. Specifically formulated for Dell printers, every Dell ink cartridge is backed by our 2-year limited warranty.²

Recycling Made Simple: All genuine Dell Ink cartridges include a prepaid label for returning used cartridges for recycling, free of charge! Visit DELL.COM/Recycling for details.

Dell Service and Support

- 1-year Advanced Exchange Service³ provided by Dell's service and support staff.
- 1-year Limited Hardware Warranty²
- Installation and Asset Tag options are also available.
- Use the Dell Online Support site for the most up-to-date drivers and technical information about your printer.
- 2-year Limited Warranty on ink cartridges.²

Visit DELL.COM/Support for details.



KEY FEATURES	<p>Print Speed (black/color) Up to 33ppm mono, up to 30ppm color – Actual print speed will vary with use</p> <p>Copy Speed Up to 25ppm mono, up to 21ppm color – Actual print speed will vary with use</p> <p>Scan Resolution Up to 1200x2400 dpi</p> <p>Maximum Monthly Duty Cycle Up to 3,000 pages per month</p> <p>Display 2-line mono LCD display</p> <p>Color Options Pink and Blue V313w color printers available in USA and Canada</p>
PAPER HANDLING	<p>Standard Input 100 sheets</p> <p>Standard Output 25 sheets</p> <p>Media Types Transparencies, Envelopes, Plain Paper, Cards, Labels, Iron-On Transfers, Photo Paper, Banner, Glossy Paper, Heavyweight Matte Paper</p> <p>Media Size Letter, Legal, Executive, Statement, A4, B5, A5, A6, Postcard (4" x 6") (4"x 8"), Index Card (3" x 5"), 3.5" x 5" (Photo), 5" x 7", Hagaki Card, L, 2L, Banner, Custom Size (up to 8½" x 17" max area)</p>
CONNECTIVITY & OS COMPATIBILITY	<p>Standard Interfaces Integrated Wi-Fi® 802.11b/g on V313w, USB 2.0 high-speed supported (Type-B connector), PictBridge™</p> <p>Compatible Client Operating Systems Microsoft® Windows® XP, Microsoft® Windows® Vista®, Microsoft® Windows® 7 and Linux (Ubuntu, SUSE, Fedora)</p> <p>Software Included ABBYY FineReader Sprint Optical Character Recognition (OCR) software</p>
WEIGHT/ DIMENSIONS	<p>Printer Dimensions (W by D by H) 18.8" x 13.3" x 7.0" (478 mm x 338 mm x 179 mm)</p> <p>Printer Weight 14.5 lbs. (6.5 kg; excluding print heads and tanks)</p>
PHOTO PRINTING	<p>Direct Photo Printing Memory Cards Supported Memory Cards, PictBridge™ and USB MicroDrive, Multi Media Card (MMC), Secure Digital (SD), Mini SD (adapter required), Memory Stick (MS), MS Pro, MS Duo (adapter required), MS Duo Pro (adapter required), XD versions M&H, Micro SD (TransFlash adapter required), MMC Mobile (adapter required), RS-MMC (adapter required), SDHC (high capacity)</p> <p>Display 2-line mono LCD display</p>
POWER CONSUMPTION & CERTIFICATIONS	<p>Other Certifications and Compliances Wi-Fi® Certification, Energy Star®-compliant</p>
CONSUMABLES	<p>Cartridges Included Single Use Standard Capacity Color, Single Use Standard Capacity Black</p> <p>Replacement Ink Cartridges Single Use ink*: Series 21 (Standard yield black or color), Series 22 (High-yield black or color) Regular Use Ink: Series 21R (Standard yield black or color) and 22R (High-yield black or color)</p>

KEY FEATURES:

- V313w comes with embedded wireless* capability
- High-speed print, scan and copy in one sleek design
- Up to 33ppm mono, up to 30ppm color – Actual print speed will vary with use
- PC-free photo printing via memory cards, PictBridge™ and USB memory devices
- 2-line mono LCD display
- Eco-Mode button enables 2-sided printing and power saving features

*Wireless Functionality: PC must have a wireless card, be connected to a wireless network, and have the printer software installed for proper function.

Retail Availability: Cartridge availability in retail stores is limited. Visit DELL.COM/NearYou for retail locations. **Single Use Ink Replacement Cartridges:** Single use tanks cost less than comparable yield regular use cartridges.

1. 3-5 day shipping available in the Continental (excluding Alaska) U.S. only.

2. For copy of limited hardware warranty, write Dell USA L.P., Attn: Warranties, One Dell Way, Round Rock, TX 78662 or visit DELL.COM/Warranty.

3. Replacement system or replacement part will be dispatched, if necessary, following phone-based troubleshooting, in advance of receipt of returned defective part or system. Subject to parts availability, geographical restrictions and terms of service contract. Service timing dependent upon time of day call placed to Dell. Defective unit must be returned. Replacements may be refurbished. U.S. only.

Microsoft and Windows are trademarks or registered trademarks of Microsoft Corporation. The Bluetooth word mark and logos are owned by Bluetooth SIG, Inc.; used by Dell Inc. under license. ©2009 Dell Inc. All rights reserved. DELLCOM90005

