




LOC	DIST	REVISIONS			
		P	LTR	DESCRIPTION	DATE
J	—		E4	REVISED PER ECO-11-005140	28MAR11

DWN	APVD
RK	HMR



- ① TO BE MEASURED WITHIN 2mm FROM **-Z-**
- 2. APPLICABLE P.C.BOARD THICKNESS: 1.6mm
- 3. THE MATING COUNTERPART PART NUMBER: 174045
- 4. RECOMMENDED MOUNTING SCREW: 3mm DIA, 6mm LENGTH TAPPING SCREW SPECIFIED IN JIS B1115, B1122 (TIGHTENING TORQUE: 0.8N-M MAX.)
- ⑤ CIRCUIT NUMBER

A-A



- ① **-Z-**面より2mmの範囲で測定
- 2. 適用プリント基板厚: 1.6mm
- 3. 嵌合相手ハウジング型番: 174045
- 4. 推奨取付ネジ: JIS B1115, B1122 タッピンネジ, ナベ2種 呼び径3, 長さ6mm (締付けトルク0.8N-M以下)
- ⑤ 回路番号: 上図参照のこと

TOLERANCE UNLESS OTHERWISE SPECIFIED: 一般公差	
0 < x ≤ 10	±0.2
10 < x ≤ 30	±0.25
30 < x ≤ 100	±0.3
ANGLE ; 角度	±3°

	PRE-TIN X 10		⑤ ⑥	黒 (BLACK)	4-174973-2
	TIN-LEAD	SELECTIVE-GOLD X 2			
	SELECTIVE-TIN	PRE-TIN	—//—	緑 (GREEN)	2-174973-4
OBSOLETE	SEE CUSTOMER DRAWING 2-174973-1				2-174973-1
	PRE-TIN		—//—	緑 (GREEN)	174973-4
	SELECTIVE-TIN (MATTE)	SELECTIVE-TIN (BRIGHT)	—//—	黒 (BLACK)	174973-3
	PRE-TIN		—//—	黒 (BLACK)	174973-2
	TIN-LEAD	SELECTIVE-GOLD X 12	① ~ ⑫	黒 (BLACK)	174973-1
	半田付け部 SOLDERING SIDE	接触部側 CONTACT SIDE	金めっき端子使用回路番号 CIRCUIT NO. OF GOLD PLATED CONTACT ⑤	色 COLOR	型番 PART NUMBER
	CONTACT 仕上げ FINISH OF CONTACT				

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.SHINOHARA 16APR02	TE Connectivity		
		CHK A.YAMAGUCHI 16APR02			
		APVD K.BETSUI 16APR02	NAME 名称		
		PRODUCT SPEC 製品規格 108-5244	040 SERIES MULTI-LOCK I/O CONN. 12Pos CAP HOUSING ASSY (VERTICAL TYPE)		
		APPLICATION SPEC 取付適用規格			
		WEIGHT 4.2 g	SIZE A3	CAGE CODE 00779	DRAWING NO 番号 C-174973
MATERIAL 材料 HOUSING: PBT CONTACT: BRASS		FINISH 仕上 SEE TABLE	SCALE 尺度 2:1		SHEET 1 OF 1
			CUSTOMER DRAWING		REV E4