




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
J	—		D2	OBSOLETE ECR-07-023693	31OCT07	AY HY



- 1. -Z- 面より2mmの範囲で測定
- 2. 適用プリント基板厚: 1.6mm
- 3. 嵌合相手ハウジング型番: 174047
- 4. 推奨取付ネジ: JIS B1115,B1122 タッピンネジ, ナベ2種 呼び径3, 長さ6mm (締付けトルク0.8N-M以下)

- 1. TO BE MEASURED WITHIN 2mm FROM -Z-
- 2. APPLICABLE P.CBOARD THICKNESS: 1.6mm
- 3. THE MATING COUNTERPART PART NUMBER: 174047
- 4. RECOMMENDED MOUTING SCREW: 3mm DIA, 6mm LENGTH TAPPING SCREW SPECIFIED IN JIS B1115, B1122 (TIGHTENING TORQUE: 0.8N-M MAX.)



OBSOLETE	SELECTIVE-TIN	PRE-TIN	20極 キャップ ハウジング アッセンブリ 20Pos. CAP HOUSING ASSEMBLY	黒 BLACK	2-174977-2
	PRE-TIN		20極 キャップ ハウジング アッセンブリ 20Pos. CAP HOUSING ASSEMBLY	緑 GREEN	174977-4
	PRE-TIN		20極 キャップ ハウジング アッセンブリ 20Pos. CAP HOUSING ASSEMBLY	黒 BLACK	174977-2
	SELECTIVE-TIN (MATTE)	SELECTIVE-TIN (BRIGHT)	20極 キャップ ハウジング アッセンブリ 20Pos. CAP HOUSING ASSEMBLY	黒 BLACK	174977-1
半田付け部 SOLDERING SIDE			接触部側 CONTACT SIDE	名称 NAME	色 COLOR
CONTACT FINISH CONTACT 仕上げ				型番 PART NUMBER	

WIRE RANGE 抱合電線断面積	INSULATION DIA 被覆外径
-----------------------	------------------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.SHINOHARA	26NOV01	Tyco Electronics AMP K.K. Kawasaki,Japan	
		CHK K.BETSUI	26NOV01		
		APVD K.BETSUI	26NOV01	NAME 名称 040 SERIES MULTI-LOCK I/O CONNECTOR 20Pos. CAP HOUSING ASSEMBLY (VERTICAL TYPE)	
		PRODUCT SPEC 製品規格 108-5244			
		APPLICATION SPEC 取付適用規格			
		WEIGHT 5.9 g		SIZE A3	CAGE CODE 00779
		CUSTOMER DRAWING		DRAWING NO 番号 C-174977	RESTRICTED TO
				SCALE 尺度 2:1	SHEET 1 OF 1
					REV D2