

Linemaster Switch Corporation

29 Plaine Hill Road POB 238

Woodstock, CT 06281-0238 USA

Toll Free: (800) 974-3668 (US Only) Telephone: (860) 974-1000 Fax: (860) 974-0691

E-Mail: service_266@linemaster.com Web site: www.linemaster.com

Item # GEM-V36, Gem-V Foot Switch



Gem-V Foot Switch

GEM-V foot switch model feature a round black actuating cap in a chrome plated heavy die cast housing with a full nonskid base pad. Moderate pressure from any direction operates the switch. Standard models supplied with cordset are wired normally open and grounded.

SPECIFICATIONS

Description	Momentary
Circuit	SPST Wired N.O.
Form	A
Electrical Rating	10 A 125-250 VAC 1/2 H.P. 125-250 VAC
Standard	EN 60529 Degree of Protection IP20
Size	3 13/16 x 1 7/32 Inch
Weight Approx.	1 lbs
Note	Supplied with 6 ft 18/3 cord without plug. Green lead grounded.
