

Item # T-91-PS, Treadlite II Foot Switch



Treadlite II Foot Switch

The handsome steel housing is painting black with nonskid base pad and foot treadle pad. The low profile and light pressure required to operate reduces operator fatigue. The maintained contact version incorporates a positive over center rocker type action.

The TWIN T-91-SC48 consists of two single models mounted on a single cast aluminum base with a divider bar between pedals which helps prevent accidental operation of both switches at one time.

SPECIFICATIONS

Description	Momentary
Circuit	SPST Wired N.O.
Form	A
Electrical Rating	3 A 30 VAC Max. Class 2 Circuits only
Standard	EN 60529 Degree of Protection IP20
Size	3 1/2 x 2 5/8 x 1 Inch
Weight Approx.	7 Oz.
Note	Supplied with 8 ft 22/1 audio cable with 2 contact 250 diameter phone plug. Not grounded