

Item # LC1D32U7, TeSys D IEC Contactor - 32A - Vac Coil

TeSys D IEC Contactor - 32A - Vac Coil

TeSys D IEC Contactor - 32A - 240Vac Coil



SPECIFICATIONS

Termination Method	Screw Clamp
Contact Rating	600V / 32A
Coil Voltage	240Vac 50/60 Hz
50/60 Hz Voltage Code	U7
Coil Consumption Inrush	70 VA
Coil Consumption Sealed	7.5 VA
Power Wire Size	#6 - #14 AWG
Power Terminal Torque	20 lb-in (2.5 Nm)
Control Wire Size	#10 - #18 AWG
Control Terminal Torque	15 lb-in (1.7 Nm)
Mounting Hardware	35mm DIN Rail, #8 screw
Weight	0.83 lb (0.375 kg)
AC1 Resistive Rating	50 Amp
AC3 Inductive Rating	32 Amp
AC3 Single Phase 115V	2 HP

AC3 Single Phase 230V	5 HP
AC3 Three Phase 200V	10 HP
AC3 Three Phase 230V	10 HP
AC3 Three Phase 460V	20 HP
AC3 Three Phase 575V	30 HP
Control Contact Rating (1NC/0NO)	A600
UL File/CCN	E164862 / NLDX
CSA File	LR43364 3211 04
Meets Standard	IEC 60647-4
CE	Yes
RoHS	Yes