








[Back](#)

Selected Cable: 17512A

End View	Plug	Cord	Connector	End View
				
5-15P	AEC-60	SJT	250A	C13

Part Number	17512A
Category	3 conductor medicord special purpose cords
Jacket Color	gray
Length Feet	10'
Length Meters	3.05
Temperature Rating	60 C°C
Packaging Units Per Carton	H-40
Color Coding	North America
AWG Stranding	18 (16x30)
Nominal OD Inch	0.325
Nominal OD millimeter	8.26
Rating	1250 Watts 10A-125V
Notes	CSA certified. Medical.

Cord View



Approvals



Qty:

Back

Volex Power Cord Products Division, 5350 Lakeview Parkway S. Drive #D Indianapolis, IN 46268
800-246-CORD. info@volexpowercords.com

Proposition 65 warning for California residents: This product contains chemicals, including lead, known to the State of California to cause (cancer, and) birth defects or other reproductive harm. Wash hands after handling.

